

PRO-IS-573

Request Samples 🕥

Check Inventory

75.0 x 8.0 x 0.8mm RoHS/RoHS II Compliant MSL Level = 1

Features

- Compact
- Thickness of 0.8 mm
- Linear Polarization
- Gain of 4.1 dBi
- Efficiency > 66% (Lower Band), 26% (Upper Band)
- Easy integration using cable and connector
- Customizable cable and Connector options

Applications

- Cellular 2G/3G/GSM and NB-IoT applications
- IoT/ M2M
- Automation/ Smart Home
- Healthcare Devices
- Hand-free/ PC Peripherals
- Remote monitoring/ Video and surveillance

Product Image





5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 11-22-21



PRO-IS-573

Request Samples 🕥

Check Inventory

75.0 x 8.0 x 0.8mm RoHS/RoHS II Compliant MSL Level = 1

Electrical Specification

Parameter	Spec	ification	Unit
Operating Frequency	791 ~ 960	$1710 \sim 1990$	MHz
Return Loss	< -7.7	< -4.5	dB
Polarization	Linear		
Peak Gain	4.1	2.8	dBi
Efficiency	>66	>26	%
Impedance	50	50	Ω

Mechanical Specification

Parameter	Specification
Antenna Dimension	75 x 8 x 0.8 mm
Cable Type	Coaxial
Cable length	60 mm
Connector Type	MHF-1 (F)
Mounting Type	Adhesive


Environmental Specification

Parameter	Specification	
Operating Temperature	-40°C to +85°C	
MSL Level	1	
RoHS/RoHS II Compliant	Yes	




5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 11-22-21



The antenna measurements were done on a standard measurement fixture - the antenna mounted in an ABS plastic box, 150x150x45 mm, connected to a PCB, 120x50 mm, with the cable fully extended.






PRO-IS-573

Request Samples (>)

Check Inventory


75.0 x 8.0 x 0.8mm RoHS/RoHS II Compliant MSL Level = 1

Return Loss



Total Radiation Efficiency

Maximum Radiation Gain






5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com


REVISED: 11-22-21













MSL Level = 1

PRO-IS-573 Request Samples Check Inventory 75.0 x 8.0 x 0.8mm RoHS/RoHS II Compliant

Packaging Information

Pieces per bag: 100 pieces

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 11-22-21