⊥ <u></u> Ω	יד וד. וויי		0	₩	≥		
	ds the second se						
			LAYOUT SHOWN A	S EXAMPLE			
	Keying Shown as example						
CHARACTERISTICS	Connector dimension	1					
Standard : Based on MIL-DTL-38999 Series III	Dim Nominal ØS 29.4 Max						
-Shell Material : Composite -Shell Plating : Nickel -Insulator : Thermoplastic	Z' 31.5 Max VV THREAD M18x1-6g		SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)				
-Contacts : Copper Alloy -Seals & Grommet : Silicon Elastomer				Intry Jurisdiction & Contro	ol List		
-Contact Plating : Gold over copper Alloy 0.8µm minimum			Country Jurisdiction & Control List FR Not Listed				
-Durability : 500 Mating cycles			PN: 8D513M04SNL				
-Delivered without Souriau contacts							
-Temperature Range : -65°C to +200°C -Salt Spray : 2000 hours		A 18-10-2	016 First Release				
Mass : 17.9 g ± 10%		ISS DATE Designed By:	E Latest modification - by Date:	CUSTOMER	MOD N°		
		TITLE					
BASIC SERIES: 8D 5 - 13 M	04 S N L	SCALE	General linea	nr NPRDS / F	PROJECT		
SHELL TYPE : Plug with RFI Shielding		/O Contacts NA	Tolerances:				
CONTACT TYPE : Standard Crimp Contact	Delivered W/O Contacts INA - + ± This document is the property of						
SHELL SIZE : 13	CONTACT TYPE : SOCKET(5		- SOURIAU WWW.SOURIAU.COIVI it must not be reproduced or				
PLATING : M = Nickel	CONTACT LAY			U DRG N°	SHEET		
		A3		M04SNL-C	1/2		
	I		000101				

-	Ŧ	۵	н г	m		0
		Contact Layout				
4	•	$ \begin{array}{c} $				
	Conta position A B C D Shell Arrangement N size no. d 13 -4	+.000 (0.00) +.150 (3.81) +.146 (3.71) +.035 (0.89) +.000 (0.00) 083 (2.11) 146 (3.71) +.035 (0.89)				
ယ						
	F					
						SOURIAU shall not be liable for an due to a use of the Products wi the Specifications issued by either o (professional recommenda
N						Count FR
					A 18-10-20	PN: 8D513N
_					ISS DATE	-
					Designed By:	Date:
_ _					SCALE	General linear Tolerances:
					SOURIA	U WWW.SOURIAU.C
					FORMAT A3	SOURIAU 8D513M
L	Н	G	F	E	D	C

