

# **XLR CABLE CONNECTORS**

### 3 PIN XLR

3 pin XLR style connectors perfect for use in audio cables and also in entry level DMX cables.



IO-XLR3-M-BK

IO-XLR3-F-BK

# **SPECIFICATIONS**

**PRODUCT** 

Gender: Male (IO-XLR3-M-BK)

Female (IO-XLR3-F-BK)

Contacts: 3

ELECTRICAL

Capacitance Between Contacts: < 2 pF

Capacitance Between Contact and Ground: < 2 pF

Contact Resistance:  $< 3 \text{ m}\Omega$ 

Insulation Resistance: ≥ 5000 MΩ

Dielectric Strength: 1500V @ 60s

Current Rating: 15A / 125V AC

**ENVIRONMENTAL** 

Standard Compliance: IEC 61076-2-103

UL Flammability Rating: **UL94V-0** 

Temperature Range:  $-40^{\circ}$ C  $\sim +70^{\circ}$  C  $(-40^{\circ}$ F  $\sim +158^{\circ}$ F)

**MECHANICAL** 

Lifetime: > 1000 Mating Cycles

Cable O.D.: 3.5mm - 8.0mm

Wiresize: 2.0mm Max (M)

2.5mm Max (F)

Wiring: Solder Contacts

Solderability: Complies with IEC

60068-2-20

**MATERIAL** 

Pins: Brass (Male)

**Phosphor Bronze (Female)** 

Pin Plating: Silver

Push Button: Nickel Plated Zinc Alloy

Latch: Tin Plated Stainless Steel

Shell: Black (Electrocoated) Zinc Alloy


Chuck: POM

**Boot: Black PVC** 




# **DRAWINGS**


#### IO-XLR3-M-BK





#### IO-XLR3-F-BK





# **FEATURES & APPLICATIONS**

The IO-XLR3-M-BK and IO-XLR3-F-BK connectors feature durable die cast zinc shells with built in latch locks which provide a reliable connection when mated with the opposite gender. They also feature a sturdy plastic insert that tightens onto the cable to provide strain relief while an additional rubber boot delivers extended support from excessive bending. The silver plated contacts ensure a great signal every time. 3 pin XLR connectors are a perfect solution for applications requiring a rugged and dependable locking connection. Because the housing construction is threaded, the connectors require no tools for assembly, making them ideal for onsite termination and allow the user to be able to troubleshoot connection issues quickly. This connector is perfect for use in balanced audio, DMX, low voltage power, and control applications where the termination method is solder cups.

These connectors are also available with gold plated contacts (IO-XLR3-M-BKAU & IO-XLR3-F-BKAU)

#### PART NUMBER BREAKDOWN

IO-XLR3-M-BK Connector Type IO-XLR3-M-BK Number of Pins IO-XLR3-M-BK Gender IO-XLR3-M-BK Body Color

#### STANDARDS & CLASSIFICATIONS



