Г	Т		Q		П			m	I	D		O
4	B Du flat	R 2.6 Max				S		ØA				
					Keving	Shown as e	kample					
	-Shell Plating -Insulator -Contacts -Seals & Grommet	: Stainless Steel : Passivated : Thermoplastic : Copper Alloy : Silicon Elastome		nimum				Image: dimension Nominal 49.2±0.3 33.32+0.1/-0.15 32.5Max 46±0.4 3+0.9/-0.1 M28x1-6g				SOURIAU sha due to a us the Specificatio (profes
	-Durability -Delivered without Sour -Temperature Range	: 500 Mating cycl	es								-2016 \TE	First Release Latest modifica
										Designed By:		Latest modifica Date
										TITLE		
<u> </u>	BASIC SERIES: SHELL TYPE : Jam nut R CONTACT TYPE : Stand SHELL SIZE : 19	-		.9 K	35 S	NL	CONTAC	Delivered W ORIEI T TYPE : SOCKET(5	NTATION : N	scale NA SOURI	J-	₩wv
	PLATING : K = Pa	assivated						CONTACT LAY	OUT : 19-35	FORMAT		
	Н		G		F			E	1	A3 D		С

 \forall

	σ		А				
				4			
LAYOUT SHOWN AS EXA	MPLE			3			
all not be liable for any non-conformity or damage use of the Products which does not comply with ons issued by either of the Parties or by a third party essional recommendation, technical notice.) Country Jurisdiction & Control List FR Not Listed PN: 8D719K35SNL							
ation - by MOD N° te: CUSTOMER DRAWING Stainless Steel Receptacle 8D series							
General linear NPRDS / PROJECT Tolerances: 859 ± This document is the property of SOURIAU V.SOURIAU.COM it must not be reproduced or communicated without permission							
SOURIAU E 8D719K35			A	SHEET 1/2			

	T G	п		
4	Contact Layout		A A A A A A A A A A A A A A A A A A A	4
	$ \begin{array}{ c c c c c c } \hline Contacts & (Insert arrangement 19-35) \\ \hline Contact & (Insert arrangement 19-35) \\ \hline Contact & V-axis & V-axi$			-
ω	$ \begin{array}{ c c c c c c c c c c c c c c c c c c c$		Dim Nominal B 33.91+0/-0.25 ØC 35.18+0.25/-0	3
	$\begin{array}{c c c c c c c c c c c c c c c c c c c $		SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)	
N	(Applicable to MIL-DTL-38999 only)ShellArrangement no.Number of contactsSize contactsService ratingContact locationSupersedes19-356622DMAllMS27530-35		Country Jurisdiction & Control List FR Not Listed	2
			PN: 8D719K35SNL A 30-09-2016 First Release ISS DATE Latest modification - by	
			Designed By: Date: CUSTOMER DRAWING TITLE Stainless Steel Receptacle 8D series	
<u> </u>			SCALE General linear NPRDS / PROJECT NA ± 859 SOURIAU WWW.SOURIAU.COM This document is the property of SOURIAU it must not be reproduced or communicated without permission communicated without permission	1
	H G	FE	FORMATSOURIAU DRG N°A3SHEET2/2DCBA	