-3.135 79.63 -2.875[73.03] "D" -2.560 [65.02] 2.400 60.96 -2x Ø.156[3.96] CARD SLOT ACCEPTS -.054" [1.37] TO .070"[1.78] 600 [15.24] THICK PCB EDAC

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER

(1)

ORIGINAL

.160 4.06 POINT OF CONTACT .330[8.38] -.370[9.4] **CARD SLOT** .150 [3.81]

Contact Dimensions: 521-P.C. Tail .025 Sq.(0.64 Sq.) - Tail LG=.150(3.81)

.100 (2.54) Contact Spacing x .200 (5.08) **Row Spacing**

INSULATOR MATERIAL: THERMOPLASTIC PBT, UL 94V-0 CONTACT MATERIAL; COPPER TIN ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR PART NUMBER: 395-046-521-204

YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO. 345-ENG-MASTER DRAWN: R.STA.MONICA DATE:MAY.16/2017 CHECKED: DATE: SCALE: 1:1 SHEET 1 OF 2 DRAWING NUMBER **ISSUE** 345-ENG-MASTER

SECTION A-A



ISSUE NUMBER

ORIGINAL

1









Contact Code 558

Contact Code 559

Contact Code 560

ACAD REFERENCE NO.

345/395 SERIES CARD EDGE CONNECTOR
CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC., AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

S	DRAWN: R.STA.MONICA	DATE:MAY.16/201	7
	CHECKED:	DATE:	
	SCALE: 1:1	SHEET 2 OF 2	2
	DRAWING NUMBER	ISSUE	
	345-ENG-MASTER	1	

345-ENG-MASTER