
-2.235 [56.77] -1.975 50.17 "D" 1.660[42.16] 1.500 [38.1] -2x Ø.156[3.96] CARD SLOT ACCEPTS -.054" [1.37] TO .070"[1.78] 600 [15.24] THICK PCB EDNG

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER ORIGINAL 1



## SECTION A-A

**Contact Dimensions:** 521-P.C. Tail .025 Sq.(0.64 Sq.) - Tail LG=.150(3.81) .100 (2.54) Contact Spacing x .200 (5.08) Row Spacing

INSULATOR MATERIAL: THERMOPLASTIC PBT, UL 94V-0 CONTACT MATERIAL; COPPER TIN ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR PART NUMBER: 395-028-521-504

YOUR CONNECTION TO QUALITY & SERVICE

**EDAC INC** TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.


ACAD REFERENCE NO. 345-ENG-MAS		
DRAWN: R.STA.MONICA	DATE:MAY.16/2017	
CHECKED:	DATE:	
SCALE: 1:1	SHEET 1 OF 2	
DRAWING NUMBER	ISSUE	
345-ENG-MASTER	1	
	1 1	





ISSUE NUMBER

ORIGINAL

1







.152[3.86] .362[9.19] .125(3.18) to .210(5.33) .045(1.14) to .060(1.52)

**Contact Code 558** 

**Contact Code 559** 

**Contact Code 560** 

345/395 SERIES CARD EDGE CONNECTOR
CONTACT CODE 555,556,558,559,560 DIMENSIONS



**EDAC INC** TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC., AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

Outside Tails

Between Tails

S	ACAD REFERE	NCE NO.	345-EN	G-MASTER
	DRAWN: R.STA	.MONICA	DATE:MAY.16/201	
	CHECKED:		DATE:	
	SCALE:	1:1	SHEET	2 OF 2
	DRAWING NUMBER		ISSUE	
	345-ENG-MASTER			1