


15920.2 PRC 2 6-12-24V AC/DC



Plug-Relay-Compact (PRC) socket base PRC with screw connection, Mounting type: Mounting rail TS 35, 2 CO contact, Input voltage: 6.12 or 24 VAC/DC

Business data

Article number	<u>15920.2</u>
Article name	PRC 2 6-12-24V AC/DC
GTIN (EAN)	4044211137359
Packaging unit	10
Quantity unit	PC
Weight per piece (not including packaging)	60.9 g
Weight per piece (including packaging)	66.32 g
Unit of weight	G
Customs number	85369010
Country of origin	IT
Product description	Relay socket base with screw connection

Technical data

Dimensions

Length	92 mm
Width	14 mm
Height TS 35 / 7.5 with BA	82 mm

Ratings

Rated voltage Un	6-12-24 VAC/DC -
Overvoltage category	III
Contamination degree	3

Connection data

Connection principle	Screw connection
Wire cross-section single core (rigid), min.	0.2 mm ²
Wire cross-section single-core (rigid), max.	2.5 mm ²
Wire cross-section stranded, min.	0.2 mm ²
Wire cross-section stranded, max.	2.5 mm ²
Stripping length	10 mm
Torque	0.5 Nm

Output data

Switching voltage / switching voltage max.	230 / 400 VAC
Contact configuration	2 CO contacts

Materials

Flammability class UL 94	V-0
Working temperature, min.	-40 °C
Working temperature, max.	70 °C

Further technical data

Status display	✓
Pinning	5 mm

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Data sheet




15920.2 PRC 2 6-12-24V AC/DC

Approvals

Standards and regulations


CE compliant	yes
--------------	-----

Media



Accessories

Cross-connector



External cross-connector insulated for Plug-Relay-Compact (PRC 2), 8-pole, can be shortened, Voltage: 250 V, Current: 10 A

Article number	Article name	GTIN (EAN)	Packaging unit
<u>15930.8</u>	AQI/PRC/8 YE	4044211137397	10

Partition plate



Partition plate for Plug-Relay-Compact (PRC) for separating relay blocks, width: 1.5 mm

Article number	Article name	GTIN (EAN)	Packaging unit
<u>15546.2</u>	TW/PRC GR	4044211118457	1 ST


Screwdriver



Screwdriver with bare blade, Colour: Black-grey

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1086.0</u>	SDB 0,6x3,5	4044211014797	1 ST

Relays




Plug-in miniature power relay, Encapsulated design with power contact, 2 CO contacts, Input voltage: 60 VAC

Article number	Article name	GTIN (EAN)	Packaging unit
<u>16124.2</u>	PRS 2/24V DC Au	4044211178222	1 ST


15920.2 PRC 2 6-12-24V AC/DC

Relays




Plug-in miniature power relay, Encapsulated design with power contact, 2 CO contact, Input voltage: 12 VDC

Article number	Article name	GTIN (EAN)	Packaging unit
<u>6482.2</u>	PRS 2/12V DC	4044211074210	1 ST



Plug-in miniature power relay, Encapsulated design with power contact, 2 CO contact, Input voltage: 24 VDC

Article number	Article name	GTIN (EAN)	Packaging unit
<u>6483.2</u>	PRS 2/24V DC	4044211074227	1 ST



Plug-in miniature power relay, Encapsulated design with power contact, 1 CO contact, Input voltage: 24 VDC

Article number	Article name	GTIN (EAN)	Packaging unit
<u>6940.0</u>	PRS 1L/24V DC	4044211076658	1 ST