<u>Contact Dimensions:</u>
544-Wire Wrap .050x.025(1.27x0.64) - Tail LG=.750(19.05)
.100 (2.54) Contact Spacing x .200 (5.08) Row Spacing

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MAST





SOUL NUMBER

.330[8.38] CARD SLOT .160[4.06] POINT OF CONTACT

DRIGINAL

1





- INSULATOR MATERIAL: THERMOPLASTIC PBT BLACK, UL 94V-0
- CONTACT MATERIAL; COPPER TIN ALLOY
 CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR
•
PART NUMBER: 395-034-544-507



TORONTO, ONTARIO CANADA

YOUR CONNECTION TO QUALITY & SERVICE WITHOUT WRI

57	CHECKED
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INCAND	SCALE:
SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE	DRAWING
MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	345

ACAD REFERENCE NO. 345-ENG-MASTER			
DRAWN: R.STA.MONICA	DATE: MA	Y.16/2017	
CHECKED:	DATE:		
SCALE: 1:1	SHEET 1	OF 2	
DRAWING NUMBER		ISSUE	
345-ENG-MASTER		1	

SECTION A-A









Contact Code 558

Contact Code 559

Contact Code 560

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0

DAP MATERIAL AVAILABLE UPON REQUEST

CONTACT MATERIAL; COPPER ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

	ACAD REFERENCE NO	. 345-ENG-MASTER
	DRAWN: R.STA.MONICA	DATE: MAY.16/2017
	CHECKED:	DATE:
	SCALE: 1:1	SHEET 2 OF 2
D	DRAWING NUMBER	ISSUE

345-ENG-MASTER