Mounting Option Contact Detail 541-Wire Wrap .025 Sq.(0.64 Sq.) - Tail LG=.760(19.30) 01-No Mounting Lugs .100 [2.54] Contact Spacing x .200 [5.08] Row Spacing 5.946 [151.03] - 5.800 [147.32] *—* 0.370 [9.40] 0.100[2.54] Card Slot Accepts .054 [1.37] to .070 [1.78] Thick P.C. Board EDRG 0.590 [14.99] SECTION A-A

See Accompanying Pages for:

- **Contact Bend Details**
- **Mounting Options**

342 / 392 Card Edge Connector Part Number: 392-114-541-201

YOUR CONNECTION TO QUALITY & SERVICE

ACAD REFERENCE NO. 342 ENG MASTER				
DRAWN: J.LEE	DATE: OCT. 06/09			
CHECKED:	DATE:			
SCALE: NTS	SHEET 1 OF 3			
DRAWING NUMBER	ISSUE			

0.410[10.41]

342 Assembly

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER. ISSUE NUMBER

ORIGINAL

1



342 / 392 Series Card Edge Connector Contact Bend Detail		ACAD REFERENCE NO. 342 ENG MASTER			
		DRAWN:	J.LEE	DATE: OCT. 06/09	
		CHECKED:		DATE:	
EDAC INC	ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS	SCALE:	NTS	SHEET :	2 OF 3
TORONTO, ONTARIO		DRAWING	NUMBER		ISSUE
YOUR CONNECTION TO QUALITY & SERVICE		3	42 Assembly		1

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER



ISSUE NUMBER

ORIGINAL

1



342 / 392 Card Edge Connector Mounting Options		ACAD REFERENCE NO. 342 ENG MASTER			
		DRAWN: J.LEE	DATE: OCT. 06/09		
		CHECKED:	DATE:		
EDAC INC	ARE THE PROPERTY OF EDAC INC.,AND — SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS	SCALE: NTS	SHEET :	3 OF 3	
TORONTO, ONTARIO		DRAWING NUMBER	•	ISSUE	
YOUR CONNECTION TO QUALITY & SERVICE		342 Assembly		1	