

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER ORIGINAL

.160 4.06 POINT OF CONTACT .330[8.38] -.370[9.4] **CARD SLOT**

SECTION A-A

<u>Contact Dimensions:</u> 520-P.C. Tail .030x.018(0.76x0.46) - Tail LG=.175(4.45) .100 (2.54) Contact Spacing x .200 (5.08) Row Spacing

INSULATOR MATERIAL: THERMOPLASTIC PBT, UL 94V-0 CONTACT MATERIAL; COPPER TIN ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR PART NUMBER: 395-037-520-404

YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.


ACAD REFERENCE NO.	345-ENG-MASTER
DRAWN: R.STA.MONICA	DATE:MAY.16/2017
CHECKED:	DATE:
SCALE: 1:1	SHEET 1 OF 2
DRAWING NUMBER	ISSUE
345-ENG-MASTER	1




ISSUE NUMBER


ORIGINAL


1





.060 .200 .235 [5.97] .635 [16.13]





Contact Code 558

Contact Code 559

Contact Code 560

ACAD REFERENCE NO

345/395 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC., AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

Outside Tails

Between Tails

<u>,</u>	THE THE THE THE	040 EI10 W/ OTEK
	DRAWN: R.STA.MONICA	DATE:MAY.16/2017
	CHECKED:	DATE:
	SCALE: 1:1	SHEET 2 OF 2
	DRAWING NUMBER	ISSUE
	345-ENG-MASTER	1

345-ENG-MASTER