Contact Dimensions: 520-P.C. Tail .030x.018(0.76x0.46) - Tail LG=.175(4.45) .100 (2.54) Contact Spacing x .200 (5.08) Row Spacing 1 -2x Ø.156[3.96] CARD SLOT ACCEPTS .054" [1.37] TO .070"[1.78] THICK PCB -5.300 [134.62] 5.460 [138.68] 5.775 146.69 POINT OF CONTACT 330[8.38] CARD SLOT 60 4.06 EDRG .175 4.45 **SECTION A-A** 600 [15.24] 6.035[153.29] 345/395 SERIES CARD EDGE CONNECTOR PART NUMBER: 395-104-520-288

INSULATOR MATERIAL: THERMOPLASTIC PBT BLACK, UL 94V-0

CONTACT MATERIAL, COPPER TIN ALLOY
CONTACT PLATING, GOLD ON THE MATING AREA TIN E

CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE



EDAC INC TORONTO, ONTARIO CANADA

YOUR CONNECTION TO QUALITY & SERVICE

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO. 345-ENG-MASTER		
DRAWN: R.STA.MONICA	DATE:MAY.16/2017	
CHECKED: DATE:		
SCALE: 1:1	SHEET 1	I OF 2
DRAWING NUMBER		ISSUE
345-ENG-MASTER		1











**Contact Code 558** 

Contact Code 559

Contact Code 560

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0

DAP MATERIAL AVAILABLE UPON REQUEST

CONTACT MATERIAL; COPPER ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

ACAD REFERENCE NO. 345-ENG-MASTER DATE:MAY.16/2017 DRAWN: R.STA.MONICA 1:1 SHEET 2 OF 2

345-ENG-MASTER