


Contact Dimensions: 521-P.C. Tail .025 Sq. (0.64 Sq.) - Tail LG. =.150 (3.81) .125 (3.18) Contact Spacing x .250 (6.35) Row Spacing






- INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0 CONTACT MATERIAL; COPPER, NICKEL, TIN_ALLOY CA-725
- CONTACT PLATING: GOLD ON THE MATING AREA, TIN-LEAD ON THE CONTACT TAILS, NICKEL UNDERPLATE

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



ORIGINAL

1



346/396 SERIES CARD EDGE CONNECTOR
PART NUMBER: 396-007-521-158



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

	ACAD REFERENCE NO.		346-ENG-MASTER	
	DRAWN: J.LEE		DATE: A	PR. 22/09
	CHECKED:		DATE:	
	SCALE: N.T.S		SHEET	OF 2
	DRAWING NUMBER 346-ENG-MASTER			ISSUE
				1

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.


Contact Code 556




ISSUE NUMBER


ORIGINAL

1





Contact Code 555



.165 [4.19] .045(1.14) to .060(1.52) Between Tails .375 [9.54] .125(3.18) to .210(5.33) **Outside Tails**

Contact Code 558

Contact Code 559

Contact Code 560

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0 CONTACT MATERIAL; COPPER, NICKEL, TIN ALLOY CA-725 CONTACT PLATING: GOLD ON THE MATING AREA, TIN-LEAD

ON THE CONTACT TAILS, NICKEL UNDERPLATE

346/396 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

	ACAD REFERENCE NO.	346-ENG-MASTER
S	DRAWN: J.LEE	DATE: APR. 22/09
3	CHECKED:	DATE:
	SCALE: 1:1	SHEET 2 OF 2
	DRAWING NUMBER	ISSUE
	346-ENG-MASTER	1