<u>Contact Dimensions:</u>
544-Wire Wrap .050x.025(1.27x0.64) - Tail LG=.750(19.05)
.100 (2.54) Contact Spacing x .200 (5.08) Row Spacing

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MAS


1220F NOWBER


160[4.06] POINT OF CONTACT

.330[8.38] CARD SLOT

ORIGINAL

1





- INSULATOR MATERIAL: THERMOPLASTIC PBT BLACK, UL 94V-0
- CONTACT MATERIAL; COPPER TIN ALLOY
 CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE






TORONTO, ONTARIO CANADA


YOUR CONNECTION TO QUALITY & SERVICE


П	
	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED
	ARE THE PROPERTY OF EDAC INC.,AND
	SHALL NOT BE REPRODUCED,OR COPIED
	OR USED AS THE BASIS FOR THE
	MANUFACTURE OR SALE OF APPARATUS
	OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.


ACAD REFERENCE NO. 345-ENG-MASTER				
DRAWN: R.STA.MONICA	DATE:MAY.16/2017			
CHECKED: DATE:				
SCALE: 1:1	SHEET 1	OF 2		
DRAWING NUMBER		ISSUE		
345-ENG-MASTER	1			

SECTION A-A









Contact Code 558

Contact Code 559

Contact Code 560

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0 DAP MATERIAL AVAILABLE UPON REQUEST

CONTACT MATERIAL; COPPER ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

ACAD REFERENCE NO. 345-ENG-MASTER DATE:MAY.16/2017 DRAWN: R.STA.MONICA 1:1 SHEET 2 OF 2

345-ENG-MASTER