

N Male to SMB Plug Adapter



RF Adapters Technical Data Sheet

PE931

Configuration

- N Male Connector 1
- SMB Plug Connector 2

- 50 Ohms
- Straight Body Geometry

Features

- N Interface compliant with MIL-STD-348
- SMB Interface compliant with MIL-STD-348
- Gold Plated Contact
- Contact Plating per MIL-G-45204

Applications

Allows Connection Between Series

General Purpose Test

Description

Pasternack's PE9314 type N male to SMB plug adapter is part of our full line of RF components available for same-day shipping. Our type N to SMB adapter has a male to plug gender configuration.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Mechanical Specifications

Size

 Length
 1.28 in [32.51 mm]

 Width
 0.8 in [20.32 mm]

 Weight
 0.075 lbs [34.02 g]

Description	Connector 1	Connector 2
Туре	N Male	SMB Plug
Polarity	Standard	Standard
Interface Specification	MIL-STD-348	MIL-STD-348

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male to SMB Plug Adapter PE9314

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451



N Male to SMB Plug Adapter



RF Adapters Technical Data Sheet

PE9314

Material Specifications

	Connector 1		Connector 2	
Description	Material	Plating	Material	Plating
Туре	N Male		SMB Plug	
Contact		Gold		Gold
		MIL-G-45204		MIL-G-45204
Insulation	PTFE		PTFE	
Body	Brass	Nickel	Brass	Nickel
		QQ-N-290		QQ-N-290
Coupling Nut	Brass	Nickel	Brass	Nickel
		QQ-N-290		QQ-N-290

Environmental Specifications

Temperature

Operating Range

-65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

N Male to SMB Plug Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male to SMB Plug Adapter PE9314

URL: https://www.pasternack.com/n-male-smb-plug-straight-adapter-pe9314-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

