Mounting Option Contact Detail 01-No Mounting Lugs 524-P.C. Tail .018 Sq.(0.46 Sq.) - Tail LG=.185(4.70) .100 [2.54] Contact Spacing x .200 [5.08] Row Spacing 5.346 [135.79] 5.200 [132.08] 0.370 [9.40] ____0.240[6.10] Point of Contact -0.100[2.54]0.410[10.41] Card Slot Accepts .054 [1.37] to .070 [1.78] Thick P.C. Board EDRG 0.590 [14.99] SECTION A-A 342 ENG MASTER 342 / 392 Card Edge Connector J.LEE DATE: OCT. 06/09 Part Number: 392-102-524-201 **See Accompanying Pages for: Contact Bend Details** SHEET 1 OF 3 NTS

CANADA

YOUR CONNECTION TO QUALITY & SERVICE

342 Assembly

Mounting Options

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER. ISSUE NUMBER

ORIGINAL

1



| 342 / 392 Series Card Edge Connector Contact Bend Detail | | ACAD REFERENCE NO. 342 ENG MASTER | | | |
|---|--|-----------------------------------|-------------|------------------|--------|
| | | DRAWN: | J.LEE | DATE: OCT. 06/09 | |
| | | CHECKED: | | DATE: | |
| TORONTO, ONTARIO | THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC. AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION. | SCALE: | NTS | SHEET : | 2 OF 3 |
| | | DRAWING | NUMBER | | ISSUE |
| YOUR CONNECTION TO QUALITY & SERVICE | | 3 | 42 Assembly | | 1 |

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER



ISSUE NUMBER

ORIGINAL

1



| 342 / 392 Card Edge Connector Mounting Options | | ACAD REFERENCE NO. 342 ENG MASTER | | | | |
|---|---|-----------------------------------|-------------------------|--------|--|--|
| | | DRAWN: J.LEE | DATE: OCT. 06/09 | | | |
| | | CHECKED: | DATE: | | | |
| TORONTO, ONTARIO | THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INCAND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION. | SCALE: NTS | SHEET : | 3 OF 3 | | |
| | | DRAWING NUMBER | • | ISSUE | | |
| YOUR CONNECTION TO QUALITY & SERVICE | | 342 Assembly | | 1 | | |