

Contact Dimensions: 541-Wire Wrap .025 Sq.(0.64 Sq.) - Tail LG=.750(19.05) .100 (2.54) Contact Spacing x .200 (5.08) Row Spacing







345/395 SERIES CARD EDGE CONNECTOR PART NUMBER: 395-050-541-888

YOUR CONNECTION TO QUALITY & SERVICE

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC.,AND
SHALL NOT BE REPRODUCED,OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO. 345-ENG-MASTER				
DRAWN: R.STA.MONICA DATE:MAY.16/201				
CHECKED:	DATE:			
SCALE: 1:1	SHEET 1	OF 2		
DRAWING NUMBER		ISSUE		
345-ENG-MASTER		1		

**SECTION A-A** 


CARD SLOT .054" [1.37] TC THICK		
1		
00[15.24]	3.335 [84.71]	

INSULATOR MATERIAL: THERMOPLASTIC PBT BLACK, UL 94V-0 CONTACT MATERIAL; COPPER TIN ALLOY

CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE


.160[4.06] POINT OF CONTACT .330[8.38] CARD SLOT





.060

.200 .235 [5.97] .635 [16.13]



.152[3.86] .362[9.19] .125(3.18) to .210(5.33) **Outside Tails** .045(1.14) to .060(1.52) Between Tails

## **Contact Code 558**

## Contact Code 559

## Contact Code 560

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0 DAP MATERIAL AVAILABLE UPON REQUEST

CONTACT MATERIAL; COPPER ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

## 345/395 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

ACAD REFERENCE NO. 345-ENG-MASTER DATE:MAY.16/2017 DRAWN: R.STA.MONICA 1:1 SHEET 2 OF 2

345-ENG-MASTER