Contact Dimensions: 541-Wire Wrap .025 Sq.(0.64 Sq.) - Tail LG=.750(19.05) .100 (2.54) Contact Spacing x .200 (5.08) Row Spacing

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MAST


ISSUE NUMBER


.160[4.06] POINT OF CONTACT

.330[8.38] CARD SLOT

ORIGINAL

1





- INSULATOR MATERIAL: THERMOPLASTIC PBT BLACK, UL 94V-0
- CONTACT MATERIAL; COPPER TIN ALLOY
 CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE





EDAC INC TORONTO, ONTARIO CANADA

YOUR CONNECTION TO QUALITY & SERVICE

| THESE DRAWINGS AND SPECIFICATIONS |
|---|
| ARE THE PROPERTY OF EDAC INC.,AND |
| THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED |
| OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION. |
| MANUFACTURE OR SALE OF APPARATUS |
| WITHOUT WRITTEN PERMISSION |
| WITHOUT WINTER I ENWISSION. |

| SECTION A-A | | | |
|---------------------|------------------|--|--|
| ACAD REFERENCE NO | . 345-ENG-MASTER | | |
| DRAWN: R.STA.MONICA | DATE:MAY.16/2017 | | |
| CHECKED: | DATE: | | |
| SCALE: 1:1 | SHEET 1 OF 2 | | |
| DRAWING NUMBER | ISSUE | | |

345-ENG-MASTER











Contact Code 558

Contact Code 559

Contact Code 560

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0

DAP MATERIAL AVAILABLE UPON REQUEST

CONTACT MATERIAL; COPPER ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

| | ACAD REFERENCE NO | . 345-ENG-MASTER |
|----|---------------------|------------------|
| 2 | DRAWN: R.STA.MONICA | DATE:MAY.16/2017 |
| J | CHECKED: | DATE: |
|) | SCALE: 1:1 | SHEET 2 OF 2 |
| ED | DRAWING NUMBER | ISSUE |

345-ENG-MASTER