

<u>Contact Dimensions:</u> 544-Wire Wrap .050x.025(1.27x0.64) - Tail LG=.750(19.05) .100 (2.54) Contact Spacing x .200 (5.08) Row Spacing

INSULATOR MATERIAL: THERMOPLASTIC PBT, UL 94V-0 CONTACT MATERIAL; COPPER TIN ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER ORIGINAL

1

.160 4.06 POINT OF CONTACT .330[8.38] -.370[9.4] **CARD SLOT**

SECTION A-A

345/395 SERIES CARD EDGE CONNECTOR PART NUMBER: 395-028-544-804



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.


ACAD REFERENCE NO.	345-ENG-MASTER		
DRAWN: R.STA.MONICA	DATE:MAY.16/2017		
CHECKED:	DATE:		
SCALE: 1:1	SHEET 1	OF 2	
DRAWING NUMBER		ISSUE	
345-ENG-MASTER	1		





ISSUE NUMBER

ORIGINAL

1







.152[3.86] .362[9.19] .125(3.18) to .210(5.33) .045(1.14) to .060(1.52)

Contact Code 558

Contact Code 559

Contact Code 560

345/395 SERIES CARD EDGE CONNECTOR
CONTACT CODE 555,556,558,559,560 DIMENSIONS



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC., AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

Outside Tails

Between Tails

S	ACAD REFERE	NCE NO.	345-EN	G-MASTER
	DRAWN: R.STA	.MONICA	DATE:MAY.16/2017	
<u> </u>	CHECKED:		DATE:	
	SCALE:	1:1	SHEET	2 OF 2
	DRAWING NUMBER		ISSUE	
	345-ENG-MASTER			1