



Banana Plug to BNC Female Adapter

RF Adapters Technical Data Sheet

PE9175

Configuration

- Banana Plug Connector 1
- BNC Female Connector 2
- Straight Body Geometry

Features

- Nickel Plated Beryllium Copper Contact

Applications

- Allows Connection Between Series
- General Purpose Test

Description

Pasternack's PE9175 Banana plug to BNC female adapter is part of our full line of RF components available for same-day shipping. Our Banana to BNC adapter has a plug to female gender configuration.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Mechanical Specifications

Size

Length	2 in [50.8 mm]
Width	0.5 in [12.7 mm]
Weight	0.027 lbs [12.25 g]

Description	Connector 1	Connector 2
Type	Banana Plug	BNC Female
Polarity	Standard	Standard

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Banana Plug to BNC Female Adapter PE9175](#)



Banana Plug to BNC Female Adapter

RF Adapters Technical Data Sheet

PE9175

Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Type	Banana Plug		BNC Female	
Contact	Beryllium Copper	Nickel	Beryllium Copper	Gold
Insulation			PTFE	
Outer Conductor			Brass	
Body	Brass	Nickel		

Compliance Certifications (see [product page](#) for current document)

Banana Plug to BNC Female Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Banana Plug to BNC Female Adapter PE9175](#)

URL: <https://www.pasternack.com/banana-plug-bnc-female-straight-adapter-pe9175-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE9175 CAD Drawing

Banana Plug to BNC Female Adapter



DWG TITLE

PE9175

NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES [mm].

REV. A

FSCM NO. 53919

CAD FILE 031212

SCALE N/A

SIZE A

2233



PASTERNAK®
 Pasternack Enterprises, Inc.
 P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | **Fax:** (949) 261-7451
Website: www.pasternack.com | **E-Mail:** sales@pasternack.com