SIEMENS

Data sheet

6GK5795-4MB00-0AA0

product type designation



Antenna ANT795-4MB

ANT795-4MB IWLAN antenna with omnidirectional Characteristic, Radially rotatable, with additional joint, incl. RSMA connector: 2/3 dBi, IP65 (-20-+60°C), 2.4/5 GHz; Wi-Fi compliance and Observe national approvals; Direct mounting on SCALANCE W with RSMA connection system; Scope of delivery: 1x ANT795-4MB, compact instructions as hard copy German/English

| radio frequencies | |
|---|----------------------|
| type of wireless network / is supported | WLAN |
| operating frequency | |
| for WLAN in 2.4 GHz frequency band | 2.4 2.5 GHz |
| for WLAN in 5 GHz frequency band 1 | 5.15 5.85 GHz |
| electrical data | |
| impedance | 50 Ω |
| polarization | linear vertical |
| radiation characteristic | omnidirectional |
| antenna gain compared to spherical radiator | |
| of the WLAN antenna / in the 2.4 GHz frequency band | 2 dB |
| of the WLAN antenna / in the 5 GHz frequency band | 3 dB |
| standing wave ratio (VSWR) / maximum | 2 |
| radiating angle of the antenna | |
| in the 2.4 GHz frequency band / horizontal | 360° |
| in the 5 GHz frequency band / horizontal | 360° |
| number of electrical connections / of the antenna | 1 |
| type of electrical connection / of the antenna | R-SMA Connector |
| design of plug-in connection | male, variable 0-90° |
| angle of inclination / downward / maximum | 0° |
| mechanical data | |
| material | |
| of outer shell | Polycarbonate |
| ambient conditions | |
| ambient temperature | |
| during operation | -20 +65 °C |
| during storage | -30 +70 °C |
| protection class IP | IP65 |
| design, dimensions and weights | |
| height | 114 mm |
| diameter | 12.9 mm |
| net weight | 21.5 g |
| fastening method | |
| mast mounting | No |
| wall mounting | No |

| roof mounting | No |
|---|---|
| directly on the device | Yes |
| product features, product functions, product components / general | |
| product feature / silicon-free | No |
| standards, specifications, approvals | |
| certificate of suitability | |
| RoHS conformity | Yes |
| wireless approval | Current national approvals can be found on the Internet under www.siemens.com/funkzulassungen |
| further information / internet-Links | |
| Internet-Link | |
| to web page: selection aid TIA Selection Tool | http://www.siemens.com/snst |
| to website: Industrial communication | http://www.siemens.com/simatic-net |
| to website: Industry Mall | https://mall.industry.siemens.com |
| to website: Information and Download Center | http://www.siemens.com/industry/infocenter |
| to website: Image database | http://automation.siemens.com/bilddb |
| to website: CAx-Download-Manager | http://www.siemens.com/cax |
| • to website: Industry Online Support | https://support.industry.siemens.com |

12/16/2020 🗗

last modified: