

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2007
 © COPYRIGHT 2007 BY - ALL RIGHTS RESERVED.

| REVISIONS | | | | |
|-----------|-----|---------------------------|-----------|----------|
| P | LTR | DESCRIPTION | DATE | DWN APVD |
| C | | REVISED PER ECO-13-016153 | 30OCT2013 | C JV DLG |
| D | | REVISED PER ECO-17-003325 | 07JUN2017 | AP DG |
| E | | REVISED PER ECN-21-103456 | 07MAY2021 | AK SZ |

PACKING UNIT:

100 KITS PACKED INTO CARDBOARD BOX

100 PIECES OF EACH COMPONENT OF THE KITS
PACKED INTO FOIL BAG AND PRINTED WITH TE - PN

VERPACKUNGSEINHEIT:

100 KITS IN KARTON VERPACKT

JEDE KOMPONENTE DER KITS ZU JE 100 STÜCK
IN KUNSTSTOFFBEUTEL VERPACKT UND MIT TE - PN BEDRUCKT

NOTE:

△ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

| 1-966 831-8 | 1-966 831-7 | 1-966 831-6 | 1-966 831-5 | 1-966 831-4 | 1-966 831-3 | 1-966 831-2 | 1-966 831-1 | 966 831-8 | 966 831-7 | 966 831-6 | 966 831-5 | 966 831-4 | 966 831-3 | 966 831-2 | 966 831-1 | 966 831-1 | 966 831-1 | | | | | | |
|--------------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|---------------------|---|--|---------|------------|--------------------------------------|--|
| 2 | 2 | 2 | 2 | 2 | 2 | 2 | 2 | - | - | - | - | - | - | - | - | - | - | 1 987 198-2 | JACK SCREW / HEBESCHRAUBE | | St | ZINCED / VERZINKT BLACK / SCHWARZ | |
| - | - | - | - | - | - | - | - | 2 | 2 | 2 | 2 | 2 | 2 | 2 | 2 | 2 | 2 | 5 747 942-1 | JACK SCREW ASSY / HEBESCHRAUBENKIT | | St / PVC | ZINCED / VERZINKT BLACK / SCHWARZ | |
| 1 | - | - | - | - | - | - | - | 1 | - | - | - | - | - | - | - | - | - | 748 464-2 | HSG ASSY. PLUG / STIFTSTECKERGEHÄUSE | 26 POS. | PA GV / St | BLACK / SCHWARZ TINNED / VERZINNT | |
| - | 1 | - | - | - | - | - | - | - | 1 | - | - | - | - | - | - | - | - | 748 630-2 | HSG ASSY. RCPT / BUCHSENSTECKERGEHÄUSE | 26 POS. | PA GV / St | BLACK / SCHWARZ TINNED / VERZINNT | |
| 1 | 1 | - | - | - | - | - | - | 1 | 1 | - | - | - | - | - | - | - | - | 747 534-2 | INSIDE SHIELD / INNERES SCHIRMBLECH | 26 POS. | St | TINNED / VERZINNT | |
| 1 | 1 | - | - | - | - | - | - | 1 | 1 | - | - | - | - | - | - | - | - | 747 533-2 | OUTSIDE SHIELD / ÄUSSERES SCHIRMBLECH | 26 POS. | St | TINNED / VERZINNT | |
| 1 | 1 | - | - | - | - | - | - | 1 | 1 | - | - | - | - | - | - | - | - | 747 934-1 | SHIELDING ENCLOSURE / ABDECKKAPPE | 26 POS. | PVC | BLACK / SCHWARZ | |
| - | - | 1 | - | - | - | - | - | - | - | 1 | - | - | - | - | - | - | - | 748 465-2 | HSG ASSY. PLUG / STIFTSTECKERGEHÄUSE | 44 POS. | PA GV / St | BLACK / SCHWARZ TINNED / VERZINNT | |
| - | - | - | 1 | - | - | - | - | - | - | - | 1 | - | - | - | - | - | - | 748 631-2 | HSG ASSY. RCPT / BUCHSENSTECKERGEHÄUSE | 44 POS. | PA GV / St | BLACK / SCHWARZ TINNED / VERZINNT | |
| - | - | 1 | 1 | - | - | - | - | - | - | 1 | 1 | - | - | - | - | - | - | 747 550-2 | INSIDE SHIELD / INNERES SCHIRMBLECH | 44 POS. | St | TINNED / VERZINNT | |
| - | - | 1 | 1 | - | - | - | - | - | - | 1 | 1 | - | - | - | - | - | - | 747 549-2 | OUTSIDE SHIELD / ÄUSSERES SCHIRMBLECH | 44 POS. | St | TINNED / VERZINNT | |
| - | - | 1 | 1 | - | - | - | - | - | - | 1 | 1 | - | - | - | - | - | - | 747 936-1 | SHIELDING ENCLOSURE / ABDECKKAPPE | 44 POS. | PVC | BLACK / SCHWARZ | |
| - | - | - | - | 1 | - | - | - | - | - | - | - | 1 | - | - | - | - | - | 748 463-3 | HSG ASSY. PLUG / STIFTSTECKERGEHÄUSE | 15 POS. | PA GV / St | BLACK / SCHWARZ TINNED / VERZINNT | |
| - | - | - | - | - | 1 | - | - | - | - | - | - | - | 1 | - | - | - | - | 748 629-2 | HSG ASSY. RCPT / BUCHSENSTECKERGEHÄUSE | 15 POS. | PA GV / St | BLACK / SCHWARZ TINNED / VERZINNT | |
| - | - | - | - | 1 | 1 | - | - | - | - | - | - | 1 | 1 | - | - | - | - | 750 442-2 | INSIDE SHIELD / INNERES SCHIRMBLECH | 15 POS. | SS | UNPLATED | |
| - | - | - | - | 1 | 1 | - | - | - | - | - | - | 1 | 1 | - | - | - | - | 747 517-2 | OUTSIDE SHIELD / ÄUSSERES SCHIRMBLECH | 15 POS. | SS | UNPLATED | |
| - | - | - | - | 1 | 1 | - | - | - | - | - | - | 1 | 1 | - | - | - | - | 747 932-1 | SHIELDING ENCLOSURE / ABDECKKAPPE | 15 POS. | PVC | BLACK / SCHWARZ | |
| - | - | - | - | - | - | 1 | - | - | - | - | - | - | - | - | - | 1 | - | 748 466-2 | HSG ASSY. PLUG / STIFTSTECKERGEHÄUSE | 62 POS. | PA GV / St | BLACK / SCHWARZ TINNED / VERZINNT | |
| - | - | - | - | - | - | - | 1 | - | - | - | - | - | - | - | - | - | 1 | 748 632-2 | HSG ASSY. RCPT / BUCHSENSTECKERGEHÄUSE | 62 POS. | PA GV / St | BLACK / SCHWARZ TINNED / VERZINNT | |
| - | - | - | - | - | - | 1 | 1 | - | - | - | - | - | - | - | - | 1 | 1 | 747 566-2 | INSIDE SHIELD / INNERES SCHIRMBLECH | 62 POS. | St | TINNED / VERZINNT | |
| - | - | - | - | - | - | 1 | 1 | - | - | - | - | - | - | - | - | 1 | 1 | 747 565-2 | OUTSIDE SHIELD / ÄUSSERES SCHIRMBLECH | 62 POS. | St | TINNED / VERZINNT | |
| - | - | - | - | - | - | 1 | 1 | - | - | - | - | - | - | - | - | 1 | 1 | 747 938-1 | SHIELDING ENCLOSURE / ABDECKKAPPE | 62 POS. | PVC | BLACK / SCHWARZ | |
| QUANTITY STÜCKZAHL | | | | | | | | | | | | | | | | | PART NO TEILENUMMER | DESCRIPTION OF THE COMPONENTS BENENNUNG DER EINZELTEILE | | | MATERIAL | SURFACE/COLOUR OBERFLÄCHE/FARBE | |

TYCO ELECTRONICS
ORDER NUMBER
BESTELLNUMMER

THIS DRAWING IS A CONTROLLED DOCUMENT. DWN M.STEIN 02NOV1995
 CHK M.DAUBER 02NOV1995

DIMENSIONS: mm TOLERANCES UNLESS OTHERWISE SPECIFIED:
 0 PLC ±
 1 PLC ±
 2 PLC ±
 3 PLC ±
 4 PLC ±
 ANGLES ±
 FINISH -

MATERIAL -

APVD -
 PRODUCT SPEC -
 APPLICATION SPEC -
 WEIGHT -

CUSTOMER DRAWING

STE TE Connectivity

NAME HD22 RECEPTACLE AND PLUG CONNECTOR KIT
 BUCHSEN- UND STIFTSTECKERKIT

SIZE A2 CAGE CODE 00779 DRAWING NO C-966831 RESTRICTED TO

SCALE DRAWING SHEET 1 OF 1 REV E