<u>Contact Dimensions:</u>
521-P.C. Tail .025 Sq.(0.64 Sq.) - Tail LG=.150(3.81)
.100 (2.54) Contact Spacing x .200 (5.08) Row Spacing 1 -2x Ø.156[3.96] CARD SLOT ACCEPTS .054" [1.37] TO .070"[1.78] THICK PCB 5.500 [139.7] 5.660 143.76 5.975 151.77 POINT OF CONTACT .330[8.38] CARD SLOT 160 4.06 EDRG [3.81] **SECTION A-A** 600 [15.24] 250 [6.35] -6.235 [158.37]

- INSULATOR MATERIAL: THERMOPLASTIC PBT BLACK, UL 94V-0
- CONTACT MATERIAL; COPPER TIN ALLOY
   CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR
PART NUMBER: 395-054-521-488



EDAC INC TORONTO, ONTARIO CANADA

OR USED AS '
MANUFACTURE
YOUR CONNECTION TO QUALITY & SERVICE WITHOUT WRITI

ONNECTOR	ACAD REFERENCE NO. 345-ENG-MASTER			
SIMINECTOR	DRAWN:	R.STA.MONICA	DATE: <b>MA</b>	Y.16/2017
,	CHECKED:		DATE:	
ESE DRAWINGS AND SPECIFICATIONS OF THE PROPERTY OF EDAC INCAND	SCALE:	1:1	SHEET '	1 OF 2
HALL NOT BE REPRODUCED, OR COPIED OF USED AS THE BASIS FOR THE	DRAWING	NUMBER		ISSUE
ANUFACTURE OR SALE OF APPARATUS	3	45-ENG-MASTER		1









**Contact Code 558** 

Contact Code 559

**Contact Code 560** 

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0

DAP MATERIAL AVAILABLE UPON REQUEST

CONTACT MATERIAL; COPPER ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

ACAD REFERENCE NO. 345-ENG-MASTER DATE:MAY.16/2017 DRAWN: R.STA.MONICA 1:1 SHEET 2 OF 2 345-ENG-MASTER