
<u>Contact Dimensions:</u>
521-P.C. Tail .025 Sq.(0.64 Sq.) - Tail LG=.150(3.81)
.100 (2.54) Contact Spacing x .200 (5.08) Row Spacing

.330[8.38] CARD SLOT 160[4.06] POINT OF CONTACT

[3.81]



ACAD REFERENCE NO. 345-ENG-MASTER 345/395 SERIES CARD EDGE CONNECTOR PART NUMBER: 395-024-521-258

YOUR CONNECTION TO QUALITY & SERVICE

THESE DRAWINGS AND SPECIFICATIONS	
ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	
WILLIAM LEIGHTEIN LEIGHIGGION.	

DRAWN: R.STA.MONICA DATE:MAY.16/2011		.16/2017
CHECKED:	DATE:	
SCALE: 1:1	SHEET 1	OF 2
DRAWING NUMBER		ISSUE
345-ENG-MASTER		1

SECTION A-A

INSULATOR MATERIAL: THERMOPLASTIC PBT BLACK, UL 94V-0


CONTACT MATERIAL; COPPER TIN ALLOY

CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE





.060 .200 .235 [5.97] .635 [16.13]



.152[3.86] .362 [9.19] .125(3.18) to .210(5.33) **Outside Tails** .045(1.14) to .060(1.52) Between Tails

Contact Code 558

Contact Code 559

Contact Code 560

- INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0 DAP MATERIAL AVAILABLE UPON REQUEST

CONTACT MATERIAL; COPPER ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING

ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

	ACAD REFERENCE NO	. 345-ENG-MASTER
	DRAWN: R.STA.MONICA	DATE: MAY.16/2017
•	CHECKED:	DATE:
	SCALE: 1:1	SHEET 2 OF 2
D	DRAWING NUMBER	ISSUE

345-ENG-MASTER