

Contact Dimensions: 540-Wire Wrap .025 Sq.(0.64 Sq.) - Tail LG=.560(14.22) .100 (2.54) Contact Spacing x .200 (5.08) Row Spacing

-.330[8.38] CARD SLOT .160[4.06] POINT OF CONTACT

150 [3.81]

1





- INSULATOR MATERIAL: THERMOPLASTIC PBT BLACK, UL 94V-0
- CONTACT MATERIAL; COPPER TIN ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

•	CARD EDGE CONNECT 395-026-540-508	OR



CANADA

YOUR CONNECTION TO QUALITY & SERVICE

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC.,AND
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED
OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION
WITHOUT WINTER I ENWISSION.

ACAD REFERENCE NO. 345-ENG-MASTER				
DRAWN: R.STA.MONICA	DATE:MAY.16/2017			
CHECKED:	DATE:			
SCALE: 1:1	SHEET 1	OF 2		
DRAWING NUMBER		ISSUE		
345-ENG-MASTER		1		

SECTION A-A











Contact Code 558

Contact Code 559

Contact Code 560

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0

DAP MATERIAL AVAILABLE UPON REQUEST

CONTACT MATERIAL; COPPER ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

	ACAD REFERENCE NO. 345-ENG-MASTER			
c	DRAWN: R.STA.MONICA	DATE:MAY.16/2017		
J	CHECKED:	DATE:		
)	SCALE: 1:1	SHEET 2 OF 2		
ED	DRAWING NUMBER	ISSUE		

345-ENG-MASTER