

<u>Contact Dimensions:</u>
544-Wire Wrap .050x.025(1.27x0.64) - Tail LG=.750(19.05)
.100 (2.54) Contact Spacing x .200 (5.08) Row Spacing

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MAS

.330[8.38] CARD SLOT 160[4.06] POINT OF CONTACT

ORIGINAL





- INSULATOR MATERIAL: THERMOPLASTIC PBT BLACK, UL 94V-0
- CONTACT MATERIAL; COPPER TIN ALLOY
 CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE






EDAC INC TORONTO, ONTARIO CANADA


YOUR CONNECTION TO QUALITY & SERVICE


THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC.,AND
SHALL NOT BE REPRODUCED,OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.


SECTION A-A					
ACAD REFERENCE NO	. 345-ENG-MASTER				
DRAWN: R.STA.MONICA	DATE:MAY.16/2017				
CHECKED:	DATE:				
SCALE: 1:1	SHEET 1 OF 2				
DRAWING NUMBER	ISSUE				

DRAWING NUMBER ISSUE
345-ENG-MASTER 1









Contact Code 558

Contact Code 559

Contact Code 560

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0 DAP MATERIAL AVAILABLE UPON REQUEST

CONTACT MATERIAL; COPPER ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

	ACAD REFE	ERENCE NO	. 345-EN	G-MASTER	
:	DRAWN: R.STA.MONICA		DATE:MAY.16/2017		
כ	CHECKED:		DATE:		
,	SCALE:	1:1	SHEET	2 OF 2	
ED	DRAWING N	NUMBER		ISSUE	

345-ENG-MASTER