

<u>Contact Dimensions:</u>
523-P.C. Tail .025 Sq.(0.64 Sq.) - Tail LG=.390(9.91)
.100 (2.54) Contact Spacing x .200 (5.08) Row Spacing



.330[8.38] CARD SLOT .160[4.06] POINT OF CONTACT

50 [3.81]





345/395 SERIES CARD EDGE CONNECTOR PART NUMBER: 395-021-523-608


YOUR CONNECTION TO QUALITY & SERVICE

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC.,AND
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED
OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION
WITHOUT WINTER I ENWISSION.

0.0 2.10 11.012.1			
DRAWN: R.STA.MONICA	DATE:MAY.16/2017		
CHECKED:	DATE:		
SCALE: 1:1	SHEET 1	OF 2	
DRAWING NUMBER		ISSUE	
345-ENG-MASTER	1		

ACAD REFERENCE NO. 345-ENG-MASTER

SECTION A-A



INSULATOR MATERIAL: THERMOPLASTIC PBT BLACK, UL 94V-0

CONTACT MATERIAL; COPPER TIN ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE









Contact Code 558

Contact Code 559

Contact Code 560

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0

DAP MATERIAL AVAILABLE UPON REQUEST

CONTACT MATERIAL; COPPER ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

ACAD REFERENCE NO. 345-ENG-MASTER DATE:MAY.16/2017 DRAWN: R.STA.MONICA 1:1 SHEET 2 OF 2

345-ENG-MASTER