**Mounting Option Contact Detail** 542-Wire Wrap .025 Sq.(0.64 Sq.) - Tail LG=.655(16.64) 01-No Mounting Lugs .100 [2.54] Contact Spacing x .200 [5.08] Row Spacing - 5.746[145.95] <del>------</del> 0.370 [9.40] 0.100[2.54] 0.410[10.41] Card Slot Accepts .054 [1.37] to .070 [1.78] Thick P.C. Board EDRG 0.590 [14.99] **SECTION A-A** 342 ENG MASTER 342 / 392 Card Edge Connector J.LEE DATE: OCT. 06/09 Part Number: 392-110-542-201 **See Accompanying Pages for: Contact Bend Details** SHEET 1 OF 3 **Mounting Options** 

YOUR CONNECTION TO QUALITY & SERVICE

342 Assembly

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER. ISSUE NUMBER

ORIGINAL

1



342 / 392 Series Card Edge Connector Contact Bend Detail		ACAD REFERENCE NO. 342 ENG MASTER			
		DRAWN:	J.LEE	DATE: OCT. 06/09	
		CHECKED:		DATE:	
TORONTO, ONTARIO	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC. AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE:	NTS	SHEET :	2 OF 3
		DRAWING	NUMBER		ISSUE
YOUR CONNECTION TO QUALITY & SERVICE		3	42 Assembly		1

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER



ISSUE NUMBER

ORIGINAL

1



342 / 392 Card Edge Connector Mounting Options		ACAD REFERENCE NO. 342 ENG MASTER				
		DRAWN: J.LEE	DATE: <b>OCT. 06/09</b>			
		CHECKED:	DATE:			
TORONTO, ONTARIO	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INCAND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE: NTS	SHEET :	3 OF 3		
		DRAWING NUMBER	•	ISSUE		
YOUR CONNECTION TO QUALITY & SERVICE		342 Assembly		1		