
THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.




ISSUE NUMBER

ORIGINAL

1





INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0 CONTACT MATERIAL; COPPER, NICKEL, TIN ALLOY CA-725 CONTACT PLATING: GOLD ON THE MATING AREA, TIN-LEAD ON THE CONTACT TAILS, NICKEL UNDERPLATE

346/396 SERIES CARD EDGE CONNECTOR PART NUMBER: 396-010-521-101

YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO.		346-ENG-MASTER	
DRAWN: .	J.LEE	DATE: AF	PR. 22/09
CHECKED:		DATE:	
SCALE:	1:1	SHEET	OF 2
DRAWING NU	MBER		ISSUE
24/ ENC MASTED			, ,

346-ENG-MASTER



SECTION A-A



ORIGINAL 1

ISSUE NUMBER

.120[3.05] .095[2.41] .170 [4.33] .245 [6.22] .125(3.18) to .210(5.33) .125(3.18) to .210(5.33) Outside Tails **Outside Tails** .045(1.14) to .060(1.52) .125(3.18) to .210(5.33) Between Tails Outside Tails

.060 [1.52] .060 [1.52] .150[3.81] .200 [5.08] .210[5.33] -.260[6.6] -.660[16.76] -.660 [16.76]

Contact Code 555

.165[4.19] .375 [9.54] .125(3.18) to .210(5.33) .125(3.18) to .210(5.33)

Contact Code 558

Contact Code 559

Contact Code 560

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0 CONTACT MATERIAL; COPPER, NICKEL, TIN ALLOY CA-725

CONTACT PLATING: GOLD ON THE MATING AREA, TIN-LEAD ON THE CONTACT TAILS, NICKEL UNDERPLATE

346/396 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

Outside Tails

Outside Tails

Contact Code 556

ACAD REFERENCE NO.	346-ENG-MASTER		
DRAWN: J.LEE	DATE: APR. 22/09		
CHECKED:	DATE:		
SCALE: 1:1	SHEET 2 OF 2		
DRAWING NUMBER	ISSUE		
344 ENIC MASTER	1 1		

346-ENG-MASTER