Contact Dimensions: 542-Wire Wrap .025 Sq.(0.64 Sq.) - Tail LG=.645(16.38) .100 (2.54) Contact Spacing x .200 (5.08) Row Spacing

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MAS


ISSUI

ORIGINAL

.160[4.06] POINT OF CONTACT

.330[8.38] CARD SLOT







IN ALLOY
THE MATING AREA, TIN PLATING
UNDERPLATE

EDAC INC TORONTO, ONTARIO CANADA

YOUR CONNECTION TO QUALITY & SERVICE WITHOUT WRITTEN PERMIS

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC., AND
SHALL NOT BE REPRODUCED, OR COPIEL
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

| ACAD REFERENCE NO. 345-ENG-MASTER | | |
|-----------------------------------|------------------|-------|
| DRAWN: R.STA.MONICA | DATE:MAY.16/2017 | |
| CHECKED: | DATE: | |
| SCALE: 1:1 | SHEET 1 | OF 2 |
| DRAWING NUMBER | | ISSUE |
| 345-ENG-MASTER | | 1 |

SECTION A-A

INSULATOR MATERIAL: THERMOPLASTIC PBT BLACK, UL 94V-0
 CONTACT MATERIAL; COPPER TIN ALLOY

 CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE











Contact Code 558

Contact Code 559

Contact Code 560

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0

DAP MATERIAL AVAILABLE UPON REQUEST

CONTACT MATERIAL; COPPER ALLOY

CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

ACAD REFERENCE NO. 345-ENG-MASTER DATE:MAY.16/2017 DRAWN: R.STA.MONICA 1:1 SHEET 2 OF 2

345-ENG-MASTER