

注記 NOTES



- 材料 MATERIAL
ウエハー PBT (ガラス 15% 入り)
WAFER G.F. 15%
UL94V-0
ピン : 黄銅, 錫メッキ
PIN : BRASS, TIN
- 嵌合相手 : 52418 シリ - ズ
MATE WITH : 52418 SERIES
- △ キンクは全ピンに交互に付加。
SET KINK ALTERNATELY TO ALL PIN.
- 各部のソリは 0.2MAX.
CAMBER : 0.2MAX.
- 本製品は、53290-**10 の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 53290-**10.
- 梱包仕様 PACKAGING
53290-**8* トレー TRAY
53290-**4* ポリ袋 POLYBAG

GENERAL TOLERANCES (UNLESS SPECIFIED)		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
10 ^{UNDER}	±0.2	DIMENSION UNITS	SCALE		
10 ^{OVER} 30 ^{UNDER}	±0.25	mm	NTS	CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#511689.	
30 ^{OVER}	±0.3	GENERAL TOLERANCES (UNLESS SPECIFIED)		PRODUCT CUSTOMER DRAWING	
ANGULAR ±3°		ANGULAR TOL	± 3.0°	DOCUMENT NUMBER	
		4 PLACES	± 0.2	SD-53290-004	
		3 PLACES	± 0.25	DOC TYPE DOC PART REVISION	
		2 PLACES	± 0.3	PSD 001 B1	
		1 PLACE	±	MATERIAL NUMBER	
		0 PLACES	±	CUSTOMER	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SHEET NUMBER	
		THIRD ANGLE PROJECTION		SEE TABLE	
		DRAWING		GENERAL MARKET	
		SERIES		1 OF 2	
		A3-SIZE			
		53290			

10 9 8 7 6 5 4 3 2 1

F
E
D
C
B
A

43	41.64	38	53290 - 2080	20
39	37.64	34	- 1880	18
37	35.64	32	- 1780	17
35	33.64	30	- 1680	16
33	31.64	28	- 1580	15
31	29.64	26	- 1480	14
29	27.64	24	- 1380	13
27	25.64	22	- 1280	12
25	23.64	20	- 1180	11
23	21.64	18	- 1080	10
21	19.64	16	- 0980	9
19	17.64	14	- 0880	8
17	15.64	12	- 0780	7
15	13.64	10	- 0680	6
13	11.64	8	- 0580	5
11	9.64	6	- 0480	4
9	7.64	4	53290 - 0380	3
C	B	A	MATERIAL NO. COLOR : NATURAL(WHITE) 色 : ナチュラル (白)	極数 CKT.

GENERAL TOLERANCES (UNLESS SPECIFIED)		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
		DIMENSION UNITS	SCALE				
10 ^{UNDER}	±0.2	mm	NTS	EC NO: 745492		2023/04/25	
10 ^{OVER} 30 ^{UNDER}	±0.25	GENERAL TOLERANCES (UNLESS SPECIFIED)		DRWN: LIKITV		2023/05/25	
30 ^{OVER}	±0.3	ANGULAR TOL ± 3.0°		CHK'D: GGA		2023/05/25	
ANGULAR ±3°		4 PLACES ± 0.2		APPR: GGA		2023/05/25	
		3 PLACES ± 0.25		INITIAL REVISION:		DOCUMENT NUMBER	
		2 PLACES ± 0.3		DRWN: JSASAMOR		SD-53290-004	
		1 PLACE ±		APPR: NUKITA		PSD 001 B1	
		0 PLACES ±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SHEET NUMBER	
		THIRD ANGLE PROJECTION		DRAWING		SERIES	
				A3-SIZE		53290	
				MATERIAL NUMBER		CUSTOMER	
				SEE TABLE		GENERAL MARKET	

DOCUMENT STATUS	P1	RELEASE DATE	2023/05/25 09:42:59
-----------------	----	--------------	---------------------

9 8 7 6 5 4 3 2 1

FORMAT: master-b-prod-A3
REVISION: 11
DATE: 2021/05/01