

Plug, solder terminal, insulated, 7.5 mm, 4-pole, straight, UK-Connector



See below:

**Approvals and Compliances**

**Description**

- Solder :  
for cable mounting
- Data and Signal transfer
- Data and Signal Connectors 4-pole , insulated , straight

**Characteristics**

- Does not comply with the JAP or BPO standard

**Weblinks**

[pdf data sheet](#), [html datasheet](#), [General Product Information](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

**Technical Data**

Diameter	7.5 mm
Number of Poles	4-pole
Ratings DC	2 A / 12 VDC
Ratings AC	2 A / 12 VAC
Dielectric Strength	1000VDC
Insulation Resistance	> 10000 MΩ @ 500VDC
Material: Housing	grey

Allowable Operation Temperature	-20 °C to 70 °C
Terminal	solder terminal
Housing	insulated
Style	straight
Lifetime	50000 Insertions




**Approvals and Compliances**

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [Details about Approvals](#)


SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

**Compliances**

The product complies with following Guide Lines

Identification	Details	Initiator	Description
	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.

## Dimensions [mm]



## All Variants

Product group	Diameter [mm]	Number of Poles	Terminal	Order Number
Data and Signal Plug/Sockets	7.5	4-pole	solder terminal	4804.1401

Availability for all products can be searched real-time: <https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

## Packaging unit

100 Pcs

## Accessories

### Description



**4804.0002**  
Sleeve brown, 5.6 mm



**4804.0053**  
Sleeve brown, 4.8 mm



**4804.0054**  
Sleeve brown, 4.2 mm

## Mating Outlets/Connectors

### Category / Description



[Data and Signal Plug/Socket Overview complete](#)

Socket, solder terminal, screened, 7.5 mm, 4-pole, straight, UK-Connector	4804.2400
Socket, solder terminal, insulated, 7.5 mm, 4-pole, straight, UK-Connector	4804.2410