

# HJM

## 1/4" x 1" to 1 1/16" Panel mount fuse holder



### Product features

- For 1/4" x 1" (6.3 mm x 25 mm) to 1/4" x 1 1/16" (6.3 mm x 27 mm) fuses
- Can be used with Bussmann Series [TCP70](#), [AGX](#), and [TDC180](#) fuses
- 250 V, 30 A rated
- Vibration resistant
- Thermoset fuse holder body and cap
- Standard thermoplastic nut
- Optional accessories available

### Applications

- Telecom power distribution
- Electronics and small appliance circuits
- Industrial control circuits
- Localized lighting controls

### Agency information


- UL Recognition: File IZLT2.E19180

### Environmental data



- +150 °C maximum
- Meets UL94HB flammability
- Terminal strength: 5 lbs
- Mounting torque: 20 in-lbs
- Salt spray (corrosion): Test condition B

**Dimensions- inches**

**HJM-R**



**HJM-HH-R**



**Ordering details**

**Fuse holder**

		<b>Catalog number</b>	<b>Ordering code</b>
<b>Part number</b>	<b>Feature</b>	<b>100 pcs per carton</b>	<b>100 pcs per carton</b>
HJM-R	Standard solder tabs	BK/HJM-R	BK-HJM-R
HJM-HH-R	1/4" Quick connects	BK/HJM-HH-R	BK-HJM-HH-R

**Optional accessories**

<b>Part number</b>	<b>Catalog number</b>	<b>Ordering code</b>	<b>Description</b>
1A4806-2	BK/1A4806-2	BK-1A4806-2	100 metal nuts
1A4287	BK/1A4287	BK-1A4287	100 plastic nuts
9435-1/2	9435-1/2	9435-1-2	10 fuse caps/carriers
9732	9732	9732	10 neoprene washers
9435-1/2	BK/9435-1/2	BK-9435-1-2	100 fuse caps/carriers
9732	BK/9732	BK-9732	100 neoprene washers

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

**Eaton**  
**Electronics Division**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com/electronics

© 2023 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. 10764 PCN23014M  
July 2023

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

