



## 3.5mm Female to 3.5mm Female Miter Right Angle Adapter

## RF Adapters Technical Data Sheet

PE91528

### Configuration

- 3.5mm Female Connector 1
- 3.5mm Female Connector 2

### **Features**

- Max VSWR of 1.35:1 up to 34.5 GHz
- 4 µin. Minimum contact plating

### **Applications**

• General Purpose Test

- 50 Ohm
- Miter Right Angle Body Geometry
- Gold over Nickel Plated Beryllium Copper Contact

#### Description

Pasternack's PE91528 3.5mm female to 3.5mm female miter right angle adapter is part of our full line of RF components available for same-day shipping. The 3.5mm connector mates mechanically with commercially available SMA and 2.92mm (K) connectors. Our 3.5mm to 3.5mm adapter has a female to female gender configuration built of durable stainless steel. PE91528 3.5mm female to 3.5mm female adapter operates to 34.5 GHz. The Pasternack RF adapter provides good VSWR of 1.35:1 maximum. This miter right angle 3.5mm to 3.5mm adapter allows for easier connections in tight spaces.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

#### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		34.5	GHz
VSWR			1.35:1	

### **Mechanical Specifications**

Size

Length 0.653 in [16.59 mm] Height 0.626 in [15.9 mm]

Description	Connector 1	Connector 2	
Туре	3.5mm Female	3.5mm Female	
Polarity	Standard	Standard	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 3.5mm Female to 3.5mm Female Miter Right Angle Adapter PE91528

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





# 3.5mm Female to 3.5mm Female Miter Right Angle Adapter

## RF Adapters Technical Data Sheet

PE91528

#### **Material Specifications**

	Connector 1		Connector 2		
Description	n Material	Plating	Material	Plating	
Туре	3.5mm Female		3.5mm Female		
Contact	Beryllium Copper	Gold over Nickel	Beryllium Copper	Gold over Nicke	
		4 μin. Minimum		4 μin. Minimum	
Insulation	Oxide-Noryl		Oxide-Noryl		
Outer Conductor	Passivated Stainless Steel		Passivated Stainless Steel		
Body	Passivated Stainless Steel		Passivated Stainless Steel		

### Compliance Certifications (see product page for current document)

3.5mm Female to 3.5mm Female Miter Right Angle Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 3.5mm Female to 3.5mm Female Miter Right Angle Adapter PE91528

URL: https://www.pasternack.com/3.5mm-female-3.5mm-female-miter-right-angle-adapter-pe91528-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

# PE91528 CAD Drawing

3.5mm Female to 3.5mm Female Miter Right Angle Adapter

