

			REVISIONS
			REV ECO DESCRIPTION DATE BY APPR
			A1 - RELEASE DRAWING 27/JUL/2021 LOUIE TOMMY
	KEY WAY	4.765	KEY WAY
	KEY-A CONFIGURATIONPART NUMBERCOLOR OF HOUSINGAT16-15PA-K003BLACKAT16-15PA-EK02GRAY	KEY-B CONFIGURATION PART NUMBER COLOR OF HOUSING AT16-15PB-K003 BLACK	KEY-C CONFIGURATIONPART NUMBERCOLOR OF HOUSINGAT16-15PC-K003BLACKAT16-15PC-EK02GREEN
			SEE CHART
			PART NUMBER DESCRIPTION TEM QUANTITY MATERIALS LIST
			UNLESS OTHERWISE SPECIFIED 1) Al dimensions are in metricinan. 1) Deamic and a follow: 1) Deamic and a follow: 2) Dea
			MATERIAL SPECIFICATIONS: UNITAC (24NULAR) CUSTOMER: THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY DESIGN FEATURES. PROCESS SPECIFICATIONS: SPECIFICATIONS AND PERPORAMENCE DATA SETZIET IFSCH NO. DWG NO: INFORMATION ONLY PROVIDENTIAL SETZIET IFSCH NO. DWG NO INFORMATION ONLY PROVIDENTIAL SETZIET IFSCH NO. D
L			NEXT ASSY: MANUFACTURING VARIATIONS. SCALE: NONE SHEET 2 OF 3

	REVISIONS
	REV ECO DESCRIPTION DATE BY APPR
	A1 - RELEASE DRAWING 27/JUL/2021 LOUIE TOMMY
	9.53
KEY WAY	
KEY-D CONFIGURATION PART NUMBER COLOR OF HOUSING	KEY-E CONFIGURATIONPART NUMBERCOLOR OF HOUSINGAT16-15PE-K003BLACKAT16-15PE-EK02GRAY
AT16-15PD-K003 BLACK AT16-15PD-EK02 BROWN	AT16-15PE-K003 BLACK AT16-15PE-EK02 GRAY
	SEE CHART DESCRIPTION TEM
	QUANTITY MATERIALS LIST
	UNLESS OTHERWISE SPECIFIED 1) All dimensions are in marking the constant of t
	Internal specifications: Internal Advance Cuistomer: Cuistomer: 15 POSITION RECEPTACLE, PIN,AT SERIES PROCESS Specifications: NPFORMATION ONLY, DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SIZE FISCH NO. [DWG NO.
	INEXT ASSY:
	NUNE SHEET 3 05 3

A Series™ - Contact Size 12 Options (Works with: AHD-6, ATP, ATHD, DuraMate and PanelMate Series)

Machined Contacts, Sockets & Pins				
Part Number	Description	Size	AWG	Туре
*AT60-204-12141-10	Male Contact - Pin, Nickel-plated	12	10-12	Machined
*AT62-203-12141-10	Female Contact - Socket, Nickel-plated	12	10-12	Machined
AT60-220-1231	Male Contact - Pin, Gold-plated	12	12-14	Machined
AT62-210-1231	Female Contact - Socket, Gold-plated	12	12-14	Machined
AT60-204-12141	Male Contact - Pin, Nickel-plated	12	12-14	Machined
AT62-203-12141	Female Contact - Socket, Nickel-plated	12	12-14	Machined

	Stamped & Formed Contacts, Sockets & Pins						
Part Number	Description	Size	AWG	Туре			
AT60-12-0244	Male Contact - Pin, Gold-plated	12	10-12	Stamped & Formed			
AT62-12-0244	Female Contact - Socket, Gold-plated	12	10-12	Stamped & Formed			
AT60-12-0222	Male Contact - Pin, Nickel-plated	12	10-12	Stamped & Formed			
AT62-12-0222	Female Contact - Socket, Nickel-plated	12	10-12	Stamped & Formed			
AT60-12-0144	Male Contact - Pin, Gold-plated	12	12-14	Stamped & Formed			
AT62-12-0144	Female Contact - Socket, Gold-plated	12	12-14	Stamped & Formed			
AT60-12-0166	Male Contact - Pin, Nickel-plated	12	12-14	Stamped & Formed			
AT62-12-0166	Female Contact - Socket, Nickel-plated	12	12-14	Stamped & Formed			

*Works with ATP Series only

DiagnosticGrade™ Machined Contacts, Sockets & Pins • Smaller AWG for Diagnostic Applications • Gold-plated • Increased Mating Cycles • Cost-effective					
Part Number	Description	Size	AWG	Туре	
65-54749	Male Contact - DiagnosticGrade™, Pin, Gold-plated	12	20	Machined	
AT62-210-1231-1820	Female Contact - DiagnosticGrade™, Socket, Gold-plated	12	20	Machined	

	Tooling - Machined Contacts					
Part Number	Description					
AUTK-12	Hand Crimp Tool, Size 12					
AUTK-100	Universal Heavy Duty Contact Crimping Tool Kit, Size 12/16/20					
CA-5D12	Universal Hand Crimp Tool, Size 12/16/20					
CA-5E12	Pneumatic Crimp Tool, Size 12/16/20					
M300-25A	Hand Crimp Tool used with Crimp Locator MFX-3966, Size 12, 10AWG					
MFX-3966	Contact Locator used with Hand Crimp Tool M300-25A, Size 12, 10AWG					

	Tooling - Stamped & Formed Contacts					
Part Number	Description					
MFX-3973	Crimp Die - Size 12					
MFX-3985	Crimp Die - Svize 12, 10-12AWG -02XX Series					
ATT-12-00	Hand Crimp Tool - Size 12, 12AWG					
ATT-12-01	Hand Crimp Tool - Size 12, 10AWG					

Cor	Contact Removal Tools (For both Machined or Stamped & Formed Contacts)					
Part Number Description						
ATRT-100	Contact and Wedgelock Extraction Tool					
AT11-337-1205	Contact Removal Tool, Plastic, Size 12					

Sealing Plugs (For both Machined or Stamped & Formed Contacts)					
Part Number	Description				
A114017	Sealing Plug, Size 12, White				

Amphenol Sine Systems 44724 Morley Drive, Clinton Township, MI 48036 USA www.amphenol-sine.com 10/2023

A Series™ - Contact Size 16 Options (Works with: AT, ATV, AHD-9, ARC, DuraMate and PanelMate Series)

Machined Contacts, Sockets & Pins						
Part Number	Description	Size	AWG	Туре		
AT60-215-1631	Male Contact - Pin, Gold-plated	16	14	Machined		
AT62-209-1631	Female Contact - Socket, Gold-plated	16	14	Machined		
AT60-215-16141	Male Contact - Pin, Nickel-plated	16	14	Machined		
AT62-209-16141	Female Contact - Socket, Nickel-plated	16	14	Machined		
AT60-202-1631	Male Contact - Pin, Gold-plated	16	16-20	Machined		
AT62-201-1631	Female Contact - Socket, Gold-plated	16	16-20	Machined		
AT60-202-16141	Male Contact - Pin, Nickel-plated	16	16-20	Machined		
AT62-201-16141	Female Contact - Socket, Nickel-plated	16	16-20	Machined		
AT60-202-1631-22	Male Contact - Pin, Gold-plated	16	22-24	Machined		
AT62-201-1631-22	Female Contact - Socket, Gold-plated	16	22-24	Machined		
AT60-202-16141-22	Male Contact - Pin, Nickel-plated	16	22-24	Machined		
AT62-201-16141-22	Female Contact - Socket, Nickel-plated	16	22-24	Machined		

	Tooling - Machined Contacts				
Part Number	Part Number Description				
AUTK-16	Hand Crimp Tool, Size 16				
AUTK-100	AUTK-100 Universal Heavy Duty Contact Crimping Tool Kit, Size 12/16/20				
CA-5D12	Universal Hand Crimp Tool, Size 12/16/20				
CA-5E12	CA-5E12 Pneumatic Crimp Tool, Size 12/16/20				

Stamped & Formed Contacts, Sockets & Pins						
Part Number	Description	Size	AWG	Туре		
AT60-14-0122	Male Contact - Pin, Nickel-plated	16	14-18	Stamped & Formed		
AT62-14-0122	Female Contact - Socket, Nickel-plated	16	14-18	Stamped & Formed		
AT60-14-0144	Male Contact - Pin, Gold-plated	16	14-18	Stamped & Formed		
AT62-14-0144	Female Contact - Socket, Gold-plated	16	14-18	Stamped & Formed		
AT60-16-0122	Male Contact - Pin, Nickel-plated	16	16-18	Stamped & Formed		
AT62-16-0122	Female Contact - Socket, Nickel-plated	16	16-18	Stamped & Formed		
AT60-16-0144	Male Contact - Pin, Gold-plated	16	16-18	Stamped & Formed		
AT62-16-0144	Female Contact - Socket, Gold-plated	16	16-18	Stamped & Formed		
AT60-16-0622	Male Contact - Pin, Nickel-plated	16	16-20	Stamped & Formed		
AT62-16-0622	Female Contact - Socket, Nickel-plated	16	16-20	Stamped & Formed		
AT60-16-0644	Male Contact - Pin, Gold-plated	16	16-20	Stamped & Formed		
AT62-16-0644	Female Contact - Socket, Gold-plated	16	16-20	Stamped & Formed		
AT60-16-0677	Male Contact - Pin, Tin-plated	16	16-20	Stamped & Formed		
AT62-16-0677	Female Contact - Socket, Tin-plated	16	16-20	Stamped & Formed		
AT60-16-0822	Male Contact - Pin, Nickel-plated	16	20-22	Stamped & Formed		
AT62-16-0822	Female Contact - Socket, Nickel-plated	16	20-22	Stamped & Formed		
AT60-16-0844	Male Contact - Pin, Gold-plated	16	20-22	Stamped & Formed		
AT62-16-0844	Female Contact - Socket, Gold-plated	16	20-22	Stamped & Formed		

Tooling - Stamped & Formed Contacts		
MFX-3950	Crimp Die - Size 16, 18-20AWG	
MFX-3953	Crimp Die - Size 16, 16-18AWG	
MFX-3975	Crimp Die - Size 16, 14-16AWG	
MFX-3990	Crimp Die - Size 16, 20-22AWG	
ATT-16-00	Hand Crimp Tool - Size 16, 14-16AWG	
ATT-16-01	Hand Crimp Tool - Size 16, 18-20AWG	
ATT-1612-03	Hand Crimp Tool - Size 16, 20-22AWG	

Contact Removal Tools (For both Machined or Stamped & Formed Contacts)		
Part Number	Description	
ATRT-100	Contact and Wedgelock Extraction Tool	
AT11-310-1605	Contact Removal Tool, Plastic, Size 16	

Sealing Plugs (For both Machined or Stamped & Formed Contacts)		
Part Number	Description	
A114017	Sealing Plug, Size 16, White	
A114017-SR	Sealing Plug, Size 16, SR01 Series, Black	
AT13-217-1605	Locking Sealing Plug, Size 16, Grey	
AT13-217-1605-SR	Locking Sealing Plug, Size 16, SR01 Series, Red	

Amphenol Sine Systems 44724 Morley Drive, Clinton Township, MI 48036 USA www.amphenol-sine.com 10-2023