



GSM UMTS antenna with omni-directional characteristic, SMA round plug, Connecting cable length: 5 m

Business data

Article number	<u>16172.2</u>
Article name	GSM-ANTENNA-EXTERNAL-SMA-5m
GTIN (EAN)	4044211187002
Packaging unit	1
Quantity unit	PC
Weight per piece (not including packaging)	262 g
Weight per piece (including packaging)	280 g
Unit of weight	G
Customs number	85291069
Country of origin	NL
Product description	GSM antenna

16172.2 GSM-ANTENNA-EXTERNAL-SMA-5m

Technical data

Dimensions

Length	80 mm
Width	80 mm
Height	45 mm
Installation height	23 mm
Drill hole diameter	17 mm

Connection data

Plug-in connector	SMA-Male
Antennengewinn max.	1 dBi
GSM frequency	800, 850, 900, 1900, 2100 MHz
Impedance	50 Ohm

Materials

Material	Nylon 6
Working temperature, min.	-40 °C
Working temperature, max.	85 °C

Further technical data

Mounting type	External, screw
Cable length	5 m
Antenna shape	Puck

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Media

16172.2 GSM-ANTENNA-EXTERNAL-SMA-5m

Accessories

##INVERSE##CONTA-ELECTRONICS



Compact reporting system for mobile networks, for monitoring analogue and digital values and remotely switching relay outputs. Mounting type: Mounting rail TS 35, Supply voltage range: 10 - 30 VDC

Article number	Article name	GTIN (EAN)	Packaging unit
<u>16099.2</u>	GSM-PRO	4044211151560	1 ST



Compact reporting system for mobile networks, for monitoring analogue and digital values and remotely switching relay outputs, incl. GSM positioning, Mounting type: Mounting rail TS 35, Supply voltage range: 10 - 30 VDC

Article number	Article name	GTIN (EAN)	Packaging unit
<u>16369.2</u>	GSM-PRO2-GPS	4044211207748	1 ST



Compact signaling system for mobile networks to monitor analog and digital values as well as remotely switch relay outputs, Mounting type: Mounting rail TS 35, Supply voltage range: 10 - 30 VDC.

Article number	Article name	GTIN (EAN)	Packaging unit
<u>16407.2</u>	GSM-PRO2E	4044211219017	1 ST



Compact reporting system for mobile networks to monitor analogue and digital values as well as remotely switch relay outputs, incl. GSM positioning, Mounting type: Mounting rail TS 35, Supply voltage range: 10 - 30 VDC

Article number	Article name	GTIN (EAN)	Packaging unit
<u>16408.2</u>	GSM-PRO2E-GPS	4044211219024	1 ST



Compact reporting system for mobile networks, for monitoring analogue and digital values and remotely switching relay outputs. Mounting type: Mounting rail TS 35, Supply voltage range: 10 - 30 VDC

Article number	Article name	GTIN (EAN)	Packaging unit
<u>16099.2</u>	GSM-PRO	4044211151560	1 ST