


## Data sheet | Item number: 267-510

Male connector with connect. for ground; without ground contact; 7-pole;  
2,50 mm<sup>2</sup>; white

[www.wago.com/267-510](http://www.wago.com/267-510)



### Data

#### Electrical data

#### Ratings per IEC/EN

Ratings per	IEC/EN 61984
Rated voltage (III/2)	500 V
Rated impulse voltage (III/2)	4 kV
Rated current	16 A
Legend (ratings)	(III / 2) $\hat{=}$ Overvoltage category III / Pollution degree 2

#### Connection data

Number of connection types	1
----------------------------	---

#### Connection 1

Connection technology	PUSH WIRE <sup>®</sup>
Strip length	11 ... 12 mm / 0.43 ... 0.47 inches
Pole number	7

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.



## Physical data

Width	35 mm / 1.378 inches
Height from the surface	18 mm / 0.709 inches
Depth	39 mm / 1.535 inches

## Material data

Note (material data)

Information on material specifications can be found here

Color	white
Material group	I
Insulation material	Polyamide (PA66)
Flammability class per UL94	V0
Clamping spring material	Chrome-nickel spring steel (CrNi)
Contact material	Electrolytic copper (E <sub>Cu</sub> )
Contact plating	Tin
Fire load	0.293 MJ
Weight	19.4 g

## Environmental requirements

Temperature stability	105 °C
-----------------------	--------

## Commercial data

Product Group	8 (Misc. Chassis Mount Blocks)
eCl@ss 10.0	27-44-03-14
eCl@ss 9.0	27-44-03-14
ETIM 8.0	EC000458
ETIM 7.0	EC000458
ECCN	NO DATA
PU (SPU)	50 pcs
Packaging type	box
Country of origin	PL
GTIN	4044918546706
Customs tariff number	85366990990

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG  
 Hansastr. 27  
 32423 Minden  
 Phone: +49571 887-0 | Fax: +49571 887-169  
 Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
 We are always happy to take your call at +49 (571) 887-44222.




## Environmental Product Compliance

RoHS Compliance Status

Compliant, No Exemption

## Approvals / Certificates

### General approvals

Logo	Approval	Additional Approval Text	Certificate name
	CCA DEKRA Certification B.V.	EN 61984	2156138.01
	CCA DEKRA Certification B.V.	IEC 61984	NL-47713
	UL UL International Germany GmbH	UL 1977	E45171
	VDE VDE Prüf- und Zertifizierungsinstitut	EN 61984	40032309

## Downloads

### Documentation

#### Additional Information

Technical Section	2019 Apr 3	pdf	Download
Technical explanations		2.1 MB	

## CAD/CAE-Data

### CAD data

2D/3D Models 267-510	URL	Download
----------------------	-----	----------

### CAE data

EPLAN Data Portal 267-510	URL	Download
---------------------------	-----	----------

ZUKEN Portal 267-510	URL	Download
----------------------	-----	----------

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG  
 Hansastr. 27  
 32423 Minden  
 Phone: +49571 887-0 | Fax: +49571 887-169  
 Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
 We are always happy to take your call at +49 (571) 887-44222.



### Asset Administration Shell

Asset Administration Shell 267-510	<a href="#">URL</a>	<a href="#">Download</a>
------------------------------------	---------------------	--------------------------

---

### Environmental Product Compliance

#### Compliance Search

Environmental Product Compliance 267-510	<a href="#">URL</a>	<a href="#">Download</a>
--	---------------------	--------------------------

Male connector with connect. for ground; without ground contact; 7-pole; 2,50 mm<sup>2</sup>;  
white

---

### Installation Notes

Subject to changes. Please also observe the further product documentation!