



| 项目   | 规格                 |
|------|--------------------|
| 额定负荷 | DC 12V 50mA        |
| 绝缘电阻 | 100MΩ min. 100v Dc |
| 耐压强度 | AC250V 50HZ 1mi n  |
| 电器寿命 | 50000次             |
| 环境温度 | -25-70℃            |
| 相对湿度 | (40℃) ≤95%         |
| 接触电阻 | 50mΩ max           |
| 行程   | 0.20±0.05mm        |
| 动作力  | 260gf±20gf         |

| PAPT NO         | TS1109-X-X                |            |
|-----------------|---------------------------|------------|
| Operating Force | 160 : 160gf ; 260 : 260gf |            |
| Height          | 38 : 3.8mm                | 65 : 6.5mm |
|                 | 43 : 4.3mm                | 70 : 7.0mm |
|                 | 45 : 4.5mm                | 75 : 7.5mm |
|                 | 50 : 5.0mm                | 80 : 8.0mm |
|                 | 55 : 5.5mm                | 85 : 8.5mm |
|                 | 60 : 6.0mm                | 90 : 9.0mm |

|    |    |       |    |    | new      |         | 2015/5/3     |                | A                      |  | 瀚源         |       |
|----|----|-------|----|----|----------|---------|--------------|----------------|------------------------|--|------------|-------|
|    |    |       |    |    | ECN BO.  |         | DESCRIPTION. |                | DATE.                  |  | REV.       |       |
|    |    |       |    |    | DESIGNED | CHECKED | APPROVAL     | DRAWING NUMBER | SCALT: 1/2             |  | SCALE: 3:1 |       |
| E  | 盖板 | 铁皮    | 1  | 镀锡 | Mikey    | Tom     | Jerry        | PART NAME      | TS1109-X-X             | UNLESS OTHERWISE SPECIFIED, TOLERANCE: | X.         | ±0.25 |
| D  | 按钮 | PPA   | 1  |    |          |         |              | MODEL NAME     | TS1109-X-X             |  | X.x        | ±0.20 |
| C  | 簧片 | 不锈钢覆银 | 1  |    |          |         |              |                |                        |  | X.xx       | ±0.15 |
| B  | 底座 | PPA   | 1  |    |          |         |              |                |                        | ANGULAIR                               | ±3         |       |
| A  | 卡件 | 黄铜    | 1  | 镀银 |          |         |              |                |                        |  |            |       |
| 序号 | 名称 | 材料    | 数量 | 备注 |          |         |              | 3RD ANGLE PROJ | HanElectricity Co.,LTD |  | FILE.NO.   |       |