



UT-F01 Cartridge fuse (fast fuse porcelain tube)

- Specifications: $\Phi 6.35 \times 31.8$ 500mA/600V
- Brand: HOLLY
- Safety certificate: CE
- Suitable products : UT61(GS) series, UT139B, UT125C
- Amount: 1pc



UT-F02 Cartridge fuse (fast fuse porcelain tube)

- Specifications: $\Phi 6.3 \times 25.4$ 10A/600V
- Brand: BUSSMANN
- Safety certificate: UL
- Suitable products : UT139 series, UT133A/B
- Amount: 1pc



UT-F03 Cartridge fuse (fast fuse porcelain tube)

- Specifications: $\Phi 6.35 \times 31.8$ 0.5A/1000V
- Brand: HOLLY
- Safety certificate: TUV
- Suitable products : UT71 series, UT81B, UT81C, UT505B
- Amount: 1pc



UT-F04 Cartridge fuse (fast fuse porcelain tube)

- Specifications: $\Phi 6 \times 32$ 0.2A/600V
- Brand: HOLLY
- Safety certificate: TUV
- Suitable products : UT139A, UT105
- Amount: 1pc



UT-F05 Cartridge fuse (fast fuse porcelain tube)

- Specifications: $\Phi 6.35 \times 31.8$ 600mA/600V
- Brand: HOLLY
- Safety certificate: TUV
- Suitable products : UT139C, UT139E, UT139S
- Amount: 1pc



UT-F06 Cartridge fuse (fast fuse porcelain tube)

- Specifications: $\Phi 6.35 \times 31.8$ 10A/600V
- Brand: HOLLY
- Safety certificate: TUV
- Suitable products : UT105, UT81B, UT81C
- Amount: 1pc



UT-F07 Cartridge fuse (fast fuse porcelain tube)

- Specifications: $\Phi 10.3 \times 38$ 10A/1000V
- Brand: HOLLY
- Safety certificate: CCC、UR/CUR、VDE
- Suitable products : UT61 series(2010 CE), UT71(CE), UT171A/B/C, UT181A
- Amount: 1pc



UT-F08 Cartridge fuse (fast fuse porcelain tube)

- Specifications: $\Phi 6.35 \times 31.8$ 600mA/1000V
- Brand: HOLLY
- Safety certificate: TUV
- Suitable products : UT61 series, UT61 series-US
- Amount: 1pc



UT-F10 Cartridge fuse (fast fuse porcelain tube)

- Specifications: $\Phi 6.35 \times 31.8$ 800mA/1000V
- Brand: HOLLY
- Safety certificate: UL
- Suitable products : UT171 series, UT181A
- Amount: 1pc