

Specification Sheet

Part Number: SAOM820HIRHSH1

Positions bundles off cross members and frame rails to prevent abrasion and chafing.

Metal insert bushing accommodates high torque installation.

Made with high impact, heat stabilized, and UV material ideal for trucking and heavy equipment environments.



Axial Oval Mount, 0.31" (8mm) Mounting Hole, PA66HIRHSUV, Black, 500/pkg

Article Number 151-29701

Type SAOM82

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton's axial oval mount stands off bundles from frame rails and cross members to prevent them from rubbing and chafing. The axial oval mount accommodates cable ties up to 0.5" wide. The hole on the mount was designed to fit a 5/16" bolt.

Short Description Axial Oval Mount, 0.31" (8mm) Mounting Hole, PA66HIRHSUV, Black, 500/pkg

Global Part Name SAOM82-PA66HIRHSUV-BK

Length L (Imperial)	1.40
Length L (Metric)	34.0
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	1.0
Width W (Metric)	26.0
Cable Ties	T50 - T250
Height H (Imperial)	1.40
Height H (Metric)	35.0
Cable Tie Width Max (Imperial)	0.5
Cable Tie Width Max (Metric)	12.7
Mounting Hole Diameter D (Imperial)	0.31
Mounting Hole Diameter D (Metric)	8.0 mm
Mounting Hole Diameter D Min (Imperial)	0.31
Mounting Hole Diameter D Max (Metric)	8.0
Stud Diameter (Metric)	8.0 mm
Stud Diameter (Imperial)	0.3125

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

