


Specification Sheet

Part Number: 155-16301



The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters.

Bundling Clip w/Oval Fir Tree, 1.6" Long, 0.02 - 0.10" Panel Thickness, PA66HIRHS, Bk, 1000/pkg

Article Number 155-16301

Type WICKELCLIP-VDS

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton Bundling Clips are designed to provide simple and easy methods for securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties.

Short Description Bundling Clip w/Oval Fir Tree, 1.6" Long, 0.02 - 0.10" Panel Thickness, PA66HIRHS, Bk, 1000/pkg

Global Part Name WICKELCLIP-VDS-PA66HIRHS-BK

Length L (Imperial)	1.6
Length L (Metric)	40.0
Fixation Method	Fir Tree for oval holes
Width W (Imperial)	0.32
Width W (Metric)	8.0
Height H (Imperial)	0.42
Height H (Metric)	12.2
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.10
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	2.5
Mounting Hole Diameter D (Imperial)	0.25 - 0.35 ";0.25 - 0.39
Mounting Hole Diameter D (Metric)	6.3 x 9.0 mm 6.3 x 10.0 mm
Mounting Hole Diameter D Min (Imperial)	0.25
Mounting Hole Diameter D Max (Imperial)	0.35
Mounting Hole Diameter D Max (Metric)	9.0

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)