

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5050663022](#)
Status: **Active**
Overview: SlimStack Board-to-Board Connectors
Description: SlimStack Board-to-Board Receptacle, 0.35mm Pitch, SSB RP Series, 0.60mm Mated Height, 2.00mm Mated Width, 30 Circuits, Armor Nail

Documents:

3D Model	Packaging Specification 5050669200-203 (PDF)
3D Model (PDF)	Datasheet (PDF)
Drawing (PDF)	Product Guide (PDF)
Product Specification 5050660000-014 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 5050660000-015 (PDF)	Reference Guide (PDF)
Application Specification 5050660000-A06 (PDF)	

General

Product Family	PCB Receptacles
Series	505066
Application	Board-to-Board
Overview	SlimStack Board-to-Board Connectors
Product Name	SlimStack
Series Name	SSB RP
UPC	191128261418

Physical

Circuits (Loaded)	30
Circuits (maximum)	30
Color - Resin	Black
Durability (mating cycles max)	30
Glow-Wire Capable	No
Mated Height	0.60mm
Mated Width	2.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	13.412/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.35mm
Pitch - Termination Interface	0.35mm
Plating min - Mating	0.100µm
Plating min - Termination	0.050µm
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Surface Mount


Electrical

Current - Maximum per Contact	0.3A, 3.0A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	5050660000-A06
---------------------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[505066 Series](#)

Mates With

SlimStack SSB RP Plug [505070](#)

Packaging Specification
Product Specification
Sales Drawing

5050669200-203
5050660000-014, 5050660000-015
5050660000-008, 5050661000-016

This document was generated on 09/15/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION