

Micro Commercial Components



Micro Commercial Components 20736 Marilla Street Chatsworth CA 91311 Phone: (818) 701-4933 Fax: (818) 701-4939

Features

- Halogen free available upon request by adding suffix "-HF"
- Low turn-on voltage
- Fast switching
- Microminiature plastic package
- This device is protected by a PN junction guard ring against
- excessive voltage, such as electrostatic discharge.
 Lead Free Finish/RoHS Compliant("P" Suffix designates RoHS Compliant. See ordering information)


Maximum Ratings


- Case: SOD-323 plastic case
- Operating Temperature: -55°C to +150°C
- Storage Temperature: -55°C to +150°C
- Thermal Resistance; 500°C/W Junction To Ambient
- Marking Code: SG
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1

Electrical Characteristics @ 25°C Unless Otherwise Specified

Continuous Reverse Voltage	V_{R}	30V	
Forward Current	_ _F	100mA	
Forward Surge	I _{FSM}	0.75A	tp=10ms
Current			
Minimum Reverse	V_{BR}	30V	I _R =100uA
Breakdown Voltage			
Maximum Leakage	I _R	1000nA	V _R =25V
Current			
Maximum Forward		550mV	l⊧=50mA
Voltage	VF	800mV	l⊧=100mA
Typical Forward	۷F	300mV	l⊧=2.0mA
Voltage		360mV	l⊧=15mA
		470mV	l⊧=50mA
		580mV	l⊧=100mA
Maximum Junction	C _{TOT}	7.0pF	Measured at
Capacitance			f=1.0MHz
			V _R =10V
Power Dissipation	P _{TOT}	250mW ¹⁾	T _c =25 ^o C

Notes: 1. Valid provided that electrodes are kept at ambient temperature





www.mccsemi.com

1 of 2



Ordering Information :

Device	Packing	
Part Number-TP	Tape&Reel: 3Kpcs/Reel	

Note : Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

*****IMPORTANT NOTICE*****

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. *Micro Commercial Components Corp*. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold *Micro Commercial Components Corp*. and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

• www.mccsemi.com