

**Micro Commercial Components** 



Micro Commercial Components 20736 Marilla Street Chatsworth CA 91311

Phone: (818) 701-4933 Fax: (818) 701-4939

# LMB2S THRU LMB10S

## **Features**

- Low Profile: Typical height of 1.4mm
- High Temperature Soldering Guaranteed:260°C/10 Second
- High surge current capability
- Halogen free available upon request by adding suffix "-HF"
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1
- Lead Free Finish/Rohs Compliant (Note1) ("P"Suffix designates Compliant. See ordering information)

### **Mechanical Data**

 Terminals:Matte tin plated leads, solderable per J-STD-002B and JESD22-B102D

MCC Part Number	Device Marking	Maximum Recurrent Peak Reverse	Maximum RMS Voltage	Maximum DC Blocking
LMB2S	LB2S	Voltage 200V	140V	Voltage 200V
LMB4S	LB4S	400V	280V	400V
LMB6S	LB6S	600V	420V	600V
LMB8S	LB8S	800V	560V	800V
LMB10S	LB10S	1000V	700V	1000V


Electrical Characteristics @ 25°C Unless Otherwise Specified

		1	-
Average Forward	$I_{F(AV)}$	1.0 A	on aluminum substrate
Current	,	0.8 A	on glass-epoxy P.C.B
Peak Forward Surge	I <sub>FSM</sub>	30A	8.3ms, half sine
Current			
Maximum			
Instantaneous	$V_{F}$	0.95V	$I_{FM} = 0.4A;$
Forward Voltage	·		$T_A = 25^{\circ}C$
Maximum DC			
Reverse Current At	$I_R$	5uA	$T_A = 25^{\circ}C$
Rated DC Blocking		100uA	T <sub>A</sub> = 125 °C
Voltage			.,, .
Typical Thermal	$R_{thJA}$	80°c/W	Note 2
Resistance	11071		
	$R_{thJL}$	25°c/W	
		2	
Rating For Fusing	l <sup>2</sup> t	3.735A <sup>2</sup> s	t<8.30ms
Operating Junction	_	-55to+150	
Temperature Range	$T_J$	°C	
-			
Storago	T <sub>STG</sub>	-65to+175	
Storage			
Temperature Range		°C	

Notes:


- 1. High Temperature Solder Exemption Applied, see EU Directive Annex Notes 7
- 2. Device mounted P.C.B with 0.47x0.47"(12mmx12mm) Copper Pads.

## 1.0 Amp Single Phase Glass Passivated Bridge Rectifier 200 to 1000 Volts





DIMENSIONS						
	INCHES		ММ			
DIM	MIN	MAX	MIN	MAX	NOTE	
Α	.197	.205	4.90	5.20		
В	.024		0.6			
C		.059		1.50		
D	.024	.032	0.60	0.80		
Е		.189		4.80		
F	.154	.161	3.90	4.10		
G		.209		5.30		
I	.236	.252	6.00	6.60		
J	.177	.185	4.30	4.70		
K	.0009	.004	0.02	0.21		
L	.006	.012	0.15	0.30		
M	.017	.019	0.25	0.70		


#### Mounting Pad Layout





**Micro Commercial Components** 













### **Ordering Information**

Device	Packing
(Part Number)-TP	Tape&Reel5Kpcs/Reel

Note: Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

#### \*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp.** reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

#### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

#### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.