

N-Ch MOSFET

General Description

The WSK180N04 is the highest performance trench N-Ch MOSFET with extreme high cell density, which provide excellent RDSON and gate charge for most of the synchronous buck converter applications.

The WSK180N04 meet the RoHS and Green Product requirement, 100% EAS guaranteed with full function reliability approved.

Features

- Advanced high cell density Trench technology
- Super Low Gate Charge
- Excellent CdV/dt effect decline
- 100% EAS Guaranteed
- Green Device Available

Product Summery


BVDSS	RDSON	ID		
40V	3.0mΩ	180A		

Applications

- Switching application
- Power Management for Inverter Systems.

TO-263 Pin Configuration





Absolute Maximum Ratings

Symbol	Parameter	Rating	Unit		
Common I	Ratings (T _C =25°C Unless Otherwise Noted)			•	
V _{DSS}	Drain-Source Voltage	40	V		
V_{GSS}	Gate-Source Voltage		±20		
TJ	Maximum Junction Temperature		175	℃	
T _{STG}	Storage Temperature Range		-55 to 175	℃	
I _S	Diode Continuous Forward Current	T _C =25℃	176	А	
Mounted o	on Large Heat Sink	•		•	
I _{DM}	Pulsed Drain Current *	T _C =25℃	648 ^{1,2}	А	
I _D	Continuous Drain Current	T _C =25℃	180	A	
		T _C =100°C	120		
P_D	Maximum Dayer Dissination	T _C =25℃	192	l w	
	Maximum Power Dissipation	T _C =100°C	96		
$R_{ heta JC}$	Thermal Resistance-Junction to Case		0.78	°C/W	
$R_{\theta JA}$	Thermal Resistance-Junction to Ambient	62.5			
Avalanche	e Ratings				
E _{AS}	Avalanche Energy, Single Pulsed	L=0.5mH	1.09 ^{1,2}	J	

NOTE:

1, Repetitive rating; pulse width limited by junction temperatur

2,Drain current is limited by junction temperature




Electrical Characteristics (T_J=25 ℃, unless otherwise noted)


Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Unit				
Static Cha	Static Characteristics									
BV _{DSS}	Drain-Source Breakdown Voltage V _{GS} =0V, I _{DS} =250μA		40	-	-	V				
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} =40V, V _{GS} =0V	-	-	1	^				
IDSS		T _J =85℃	-	-	10	μΑ				
V _{GS(th)}	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_{DS}=250\mu A$	2.0	3.0	4.0	V				
I _{GSS}	Gate Leakage Current	V _{GS} =±20V, V _{DS} =0V	-	-	±100	nA				
R _{DS(ON)} *	Drain-Source On-state Resistance	V _{GS} =10V, I _{DS} =88A	-	3.0	3.6	mΩ				
Diode Cha	Diode Characteristics									
V _{SD} *	Diode Forward Voltage	I _{SD} =88A, V _{GS} =0V	-	0.8	1.2	V				
t _{rr}	Reverse Recovery Time	I _{SD} =88A, dI _{SD} /	-	27	-	ns				
Q _{rr}	Reverse Recovery Charge	dt=100A/μs	-	50	-	nC				
Dynamic C	Characteristics		•	•	•	•				
R_{G}	Gate Resistance	V _{GS} =0V,V _{DS} =0V,F=1MHz	-	1.1	-	Ω				
C _{iss}	Input Capacitance	V _{GS} =0V,	-	4426	-	pF				
C _{oss}	Output Capacitance	V _{DS} =25V,	-	1027	-					
C _{rss}	Reverse Transfer Capacitance	Frequency=1.0MHz	-	537	-					
t _{d(ON)}	Turn-on Delay Time		-	27	-					
T _r	Turn-on Rise Time	V_{DD} =20V, R _G =6 Ω , I_{DS} =88A, V _{GS} =10V ,	-	18	-	- ns				
t _{d(OFF)}	Turn-off Delay Time		-	41	-					
T _f	Turn-off Fall Time		-	53	-					
Gate Char	ge Characteristics	•	-	-	-	-				
Q_g	Total Gate Charge		-	121	-					
Q_{gs}	Gate-Source Charge	V _{DS} =32V, V _{GS} =10V, I _{DS} =88A	-	28	-	nC				
Q_{gd}	Gate-Drain Charge	35 111, 153 007.	-	34	-					
	-				-					


Note * : Pulse test ; pulse width $\leq\!300\mu s,$ duty cycle $\!\leq\!2\%.$




Typical Characteristics













Typical Characteristics


Drain-Source On Resistance




Source-Drain Diode Forward










Gate Charge





















TO-263-2L







COMMON DIMENSIONS

SYMBOL	MM			INCH			
STIVIBUL	MIN	NOM	MAX	MIN	NOM	MAX	
Α	4.40	4.57	4.70	0.173	0.180	0.185	
A1	1.22	1.27	1.32	0.048	0.050	0.052	
A2	2.59	2.69	2.79	0.102	0.106	0.110	
A3	0.00	0.10	0.20	0.000	0.004	0.008	
b	0.77	0.813	0.90	0.030	0.032	0.035	
b1	1.20	1.270	1.36	0.047	0.050	0.054	
С	0.34	0.381	0.47	0.013	0.015	0.019	
D1	8.60	8.70	8.80	0.339	0.343	0.346	
Ε	10.00	10.16	10.26	0.394	0.400	0.404	
E2	10.00	10.10	10.20	0.394	0.398	0.402	
е	2.54 BSC			0.100 BSC			
Н	14.70	15.10	15.50	0.579	0.594	0.610	
H2	1.17	1.27	1.40	0.046	0.050	0.055	
L	2.00	2.30	2.60	0.079	0.091	0.102	
L1	1.45	1.55	1.70	0.057	0.061 0.067		
L2		2.50	REF	0.098 REF			
L4	0.25 BSC			0.010 BSC			
	0°	5°	8°	0°	5°	8°	
1	5°	7°	9°	5°	7°	9°	
2	1°	3°	5°	1°	3°	5°	
ФР1	1.40	1.50	1.60	0.055	0.059	0.063	
DEP	0.05	0.10	0.20	0.002	0.004	800.0	



Attention

- 1, Any and all Winsok power products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your Winsok power representative nearest you before using any Winsok power products described or contained herein in such applications.
- 2, Winsok power assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all Winsok power products described or contained herein.
- 3, Specifications of any and all Winsok power products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- 4, Winsok power Semiconductor CO., LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- 5,In the event that any or all Winsok power products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- 6, No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of Winsok power Semiconductor CO., LTD.
- 7, Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. Winsok power believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- 8, Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the Winsok power product that you Intend to use.
- 9, this catalog provides information as of Sep.2014. Specifications and information herein are subject to change without notice.