


High Performance Schottky Rectifier, 2 x 6 A



PRODUCT SUMMARY				
Package	D-PAK (TO-252AA)			
I _{F(AV)}	2 x 6 A			
V_{R}	30 V			
V _F at I _F	0.37 V			
I _{RM}	58 mA at 125 °C			
T _J max.	150 °C			
Diode variation	Common cathode			
E _{AS}	10 mJ			

FEATURES

- Low forward voltage drop
- Guard ring for enhanced ruggedness and long term reliability



FREE

- Popular D-PAK outline
- Center tap configuration
- · Small foot print, surface mountable
- High frequency operation
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

DESCRIPTION

The VS-12CWQ03FN-M3 surface mount, center tap, Schottky rectifier series has been designed for applications requiring low forward drop and small foot prints on PC board. Typical applications are in disk drives, switching power supplies, converters, freewheeling diodes, battery charging, and reverse battery protection.

MAJOR RATINGS AND CHARACTERISTICS						
SYMBOL	CHARACTERISTICS	VALUES	UNITS			
I _{F(AV)}	Rectangular waveform	12	A			
V_{RRM}		30	V			
I _{FSM}	t _p = 5 µs sine	320	A			
V _F	6 A _{pk} , T _J = 125 °C (per leg)	0.37	V			
TJ	Range	-55 to +150	°C			

VOLTAGE RATINGS						
PARAMETER	SYMBOL	VS-12CWQ03FN-M3	UNITS			
Maximum DC reverse voltage	V _R	20	V			
Maximum working peak reverse voltage	V _{RWM}	- 30	V			

ABSOLUTE MAXIMUM RATINGS							
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS		
Maximum average per leg		50 % duty cycle at T _C = 135 °C, rectangular waveform		6	А		
See fig. 5 per device	I _{F(AV)}			12	^		
Maximum peak one cycle non-repetitive surge current per leg		5 μs sine or 3 μs rect. pulse Follo		320	Α		
See fig. 7	IFSM	10 ms sine or 6 ms rect. pulse	load condition and with rated V _{RRM} applied	130	^		
Non-repetitive avalanche energy per leg	E _{AS}	T _J = 25 °C, I _{AS} = 2.0 A, L = 5 mH		10	mJ		
Repetitive avalanche current per leg	I _{AR}	Current decaying linearly to zero in 1 μ s Frequency limited by T _J maximum V _A = 1.5 x V _R typical		2.0	Α		



ELECTRICAL SPECIFICATIONS						
PARAMETER	SYMBOL	TEST CO	VALUES	UNITS		
		6 A	T _{.1} = 25 °C	0.47	V	
Maximum forward voltage drop per leg	V _{FM} ⁽¹⁾	12 A	11 = 23 0	0.55		
See fig. 1	V FM (*)	6 A	T _{.1} = 125 °C	0.37		
3		12 A	1j = 125 C	0.49		
Maximum reverse leakage current per leg	I _{RM} ⁽¹⁾	T _J = 25 °C	V _B = Rated V _B	3	- mA	
See fig. 2	'RM ` '	T _J = 125 °C	v _R = nateu v _R	58		
Threshold voltage	V _{F(TO)}	T T		0.196	V	
Forward slope resistance	r _t	$T_J = T_J$ maximum	21.66	mΩ		
Typical junction capacitance per leg	C _T	V _R = 5 V _{DC} (test signal range	590	pF		
Typical series inductance per leg	L _S	Measured lead to lead 5 n	Measured lead to lead 5 mm from package body 5.			

Note

 $^{^{(1)}\,}$ Pulse width < 300 µs, duty cycle < 2 %

THERMAL - MECHANICAL SPECIFICATIONS						
PARAMETER		SYMBOL	TEST CONDITIONS	VALUES	UNITS	
Maximum junction and storage temperature range		T _J ⁽¹⁾ , T _{Stg}		-55 to +150	°C	
Maximum thermal resistance,	per leg	D	DC operation	3.0	°C/W	
junction to case	per device	R_{thJC}	See fig. 4	1.5	C/ VV	
Approximate weight				0.3	g	
Approximate weight				0.01	OZ.	
Marking device			Case style D-PAK (similar to TO-252AA)	12CW(Q03FN	

Note

$$^{(1)} \quad \frac{dP_{tot}}{dT_J} < \frac{1}{R_{thJA}} \quad \text{thermal runaway condition for a diode on its own heatsink}$$




Fig. 1 - Maximum Forward Voltage Drop Characteristics (Per Leg)




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage (Per Leg)




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage (Per Leg)




Fig. 4 - Maximum Thermal Impedance Z_{thJC} Characteristics (Per Leg)

www.vishay.com

Vishay Semiconductors




Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current (Per Leg)




Fig. 6 - Forward Power Loss Characteristics (Per Leg)





Fig. 7 - Maximum Non-Repetitive Surge Current (Per Leg)

Note



ORDERING INFORMATION TABLE





1 - Vishay Semiconductors product

Current rating (12 A)

Center tap configuration

Package identifier:

W = D-PAK

5 - Schottky "Q" series

6 - Voltage rating (03 = 30 V)

7 - FN = TO-252AA

8 - • None = tube

• TR = tape and reel

• TRL = tape and reel (left oriented)

• TRR = tape and reel (right oriented)

9 - Environmental digit:

-M3 = halogen-free, RoHS-compliant and terminations lead (Pb)-free

ORDERING INFORMATION (Example)						
PREFERRED P/N	QUANTITY PER T/R	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION			
VS-12CWQ03FN-M3	75	3000	Antistatic plastic tube			
VS-12CWQ03FNTR-M3	2000	2000	13" diameter reel			
VS-12CWQ03FNTRL-M3	3000	3000	13" diameter reel			
VS-12CWQ03FNTRR-M3	3000	3000	13" diameter reel			

LINKS TO RELATED DOCUMENTS					
Dimensions <u>www.vishay.com/doc?95627</u>					
Part marking information	www.vishay.com/doc?95176				
Packaging information	www.vishay.com/doc?95033				



D-PAK (TO-252AA) "M"

DIMENSIONS in millimeters and inches



SYMBOL MILLIME		IETERS	INC	HES	NOTES
STIVIBUL	MIN.	MAX.	MIN.	MAX.	NOTES
Α	2.18	2.39	0.086	0.094	
A1	-	0.13	-	0.005	
b	0.64	0.89	0.025	0.035	
b2	0.76	1.14	0.030	0.045	
b3	4.95	5.46	0.195	0.215	3
С	0.46	0.61	0.018	0.024	
c2	0.46	0.89	0.018	0.035	
D	5.97	6.22	0.235	0.245	5
D1	5.21	-	0.205	1	3
Е	6.35	6.73	0.250	0.265	5
E1	4.32	-	0.170	-	3

SYMBOL	MILLIN	IETERS	INC	HES	NOTES
STINIBOL	MIN.	MAX.	MIN.	MAX.	NOTES
е	2.29	BSC	0.090	BSC	
Н	9.40	10.41	0.370	0.410	
L	1.40	1.78	0.055	0.070	
L1	2.74 BSC		0.108 REF.		
L2	0.51	BSC	0.020 BSC		
L3	0.89	1.27	0.035	0.050	3
L4	-	1.02	-	0.040	
L5	1.14	1.52	0.045	0.060	2
Ø	0°	10°	0°	10°	
Ø1	0°	15°	0°	15°	
Ø2	25°	35°	25°	35°	

Notes

- (1) Dimensioning and tolerancing as per ASME Y14.5M-1994
- (2) Lead dimension uncontrolled in L5
- (3) Dimension D1, E1, L3 and b3 establish a minimum mounting surface for thermal pad
- (4) Section C C dimension apply to the flat section of the lead between 0.13 and 0.25 mm (0.005 and 0.10") from the lead tip
- (5) Dimension D, and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- (6) Dimension b1 and c1 applied to base metal only
- (7) Datum A and B to be determined at datum plane H
- (8) Outline conforms to JEDEC® outline TO-252AA



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.