

### 5N65K-MTQ

### Power MOSFET

## 5A, 650V N-CHANNEL POWER MOSFET


#### DESCRIPTION


The UTC **5N65K-MTQ** is a high voltage power MOSFET designed to have better characteristics, such as fast switching time, low gate charge, low on-state resistance and high rugged avalanche characteristics. This power MOSFET is usually used in high speed switching applications at power supplies, PWM motor controls, high efficient DC to DC converters and bridge circuits.

#### FEATURES

- \*  $R_{DS(ON)}$  < 2.2 $\Omega$  @  $V_{GS}$  = 10 V,  $I_D$  = 2.5 A
- \* Fast Switching Capability
- \* Improved dv/dt Capability, High Ruggedness


#### SYMBOL






#### ORDERING INFORMATION

Ordering Number		Daakaga	Pin Assignment			Dooking	
Lead Free	Halogen Free	Package	1	2	3	Packing	
5N65KL-TA3-T	5N65KG-TA3-T	TO-220	G	D	S	Tube	
5N65KL-TF3-T	5N65KG-TF3-T	TO-220F	G	D	S	Tube	
5N65KL-TF1-T	5N65KG-TF1-T	TO-220F1	G	D	S	Tube	
5N65KL-TF2-T	5N65KG-TF2-T	TO-220F2	G	D	S	Tube	
5N65KL-TF3-T	5N65KG-TF3-T	TO-220F3	G	D	S	Tube	
5N65KL-TM3-T	5N65KG-TM3-T	TO-251	G	D	S	Tube	
5N65KL-TMS-T	5N65KG-TMS-T	TO-251S	G	D	S	Tube	
5N65KL-TMS2-T	5N65KG-TMS2-T	TO-251S2	G	D	S	Tube	
5N65KL-TMS4-T	5N65KG-TMS4-T	TO-251S4	G	D	S	Tube	
5N65KL-TN3-R	5N65KG-TN3-R	TO-252	G	D	S	Tape Reel	
5N65KL-TND-R	L-TND-R 5N65KG-TND-R		G	D	S	Tape Reel	
Note: Pin Assignment: G: Gate D: Drain S: Source							



#### MARKING





PARAMETER		SYMBOL	RATINGS	UNIT
Drain-Source Voltage		V <sub>DSS</sub>	650	V
Gate-Source Voltage		V <sub>GSS</sub>	±30	V
Continuous Drain Current		I <sub>D</sub>	5	A
Pulsed Drain Current (Note 2)		I <sub>DM</sub>	20	A
Avalanche Energy	Single Pulsed (Note 3)	E <sub>AS</sub>	264	mJ
Peak Diode Recovery dv/dt (Note 4)		dv/dt	6.5	V/ns
Power Dissipation	TO-220		108	
	TO-220F/TO-220F1 TO-220F3		36	
	TO-220F2	PD	38	W
	TO-251/TO-251S TO-251S2/TO-251S4 TO-252/TO-252D		54	
Junction Temperature		TJ	+150	°C
Operation Temperature		T <sub>OPR</sub>	-55 ~ +150	°C
Storage Temperature		T <sub>STG</sub>	-55 ~ +150	°C

#### ■ ABSOLUTE MAXIMUM RATINGS (T<sub>c</sub> = 25°C, unless otherwise specified)

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.

2. Repetitive Rating: Pulse width limited by maximum junction temperature.

3. L=25mH, I<sub>AS</sub>=4.6A, V<sub>DD</sub>=50V, R<sub>G</sub>=25  $\Omega$ , Starting T<sub>J</sub> = 25°C

4. I<sub>SD</sub> $\leq$ 5A, di/dt $\leq$ 200A/µs, V<sub>DD</sub> $\leq$  BV<sub>DSS</sub>, Starting T<sub>J</sub> = 25°C

#### THERMAL RESISTANCES CHARACTERISTICS

PARAMETER		SYMBOL	RATINGS	UNIT	
Junction to Ambient	TO-220/TO-220F TO-220F1/TO-220F2 TO-220F3	0	62.5	°C/W	
	TO-251/TO-251S TO-251S2/TO-251S4 TO-252/TO-252D	$\theta_{JA}$	110	°C/W	
Junction to Case	TO-220		1.15	°C/W	
	TO-220F/TO-220F1 TO-220F3		3.47	°C/W	
	TO-220F2	θ <sub>JC</sub>	3.28	°C/W	
	TO-251/TO-251S TO-251S2/TO-251S4 TO-252/TO-252D		2.3	°C/W	



# 5N65K-MTQ

#### ■ ELECTRICAL CHARACTERISTICS (T<sub>c</sub> = 25°C unless otherwise specified)


			,				
PARAMETER		SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
OFF CHARACTERISTICS							
Drain-Source Breakdown Voltage		BV <sub>DSS</sub>	V <sub>GS</sub> =0V, I <sub>D</sub> = 250µA	650			V
Drain-Source Leakage Current		I <sub>DSS</sub>	V <sub>DS</sub> =650V, V <sub>GS</sub> = 0V			1	μA
Gate-Source Leakage Current	Forward	- I <sub>GSS</sub>	V <sub>GS</sub> =30V, V <sub>DS</sub> = 0V			100	nA
	Reverse		V <sub>GS</sub> =-30V, V <sub>DS</sub> = 0V			-100	ΠA
ON CHARACTERISTICS							
Gate Threshold Voltage		V <sub>GS(TH)</sub>	$V_{DS} = V_{GS}, I_{D} = 250 \mu A$	2.0		4.0	V
Static Drain-Source On-State Resistance		R <sub>DS(ON)</sub>	V <sub>GS</sub> =10V, I <sub>D</sub> = 2.5A			2.2	Ω
DYNAMIC CHARACTERISTICS							
Input Capacitance		CISS			636		pF
Output Capacitance		C <sub>OSS</sub>	$V_{DS} = 25V, V_{GS} = 0V,$		69		pF
Reverse Transfer Capacitance		C <sub>RSS</sub>	f = 1.0MHz		4.3		pF
SWITCHING CHARACTERISTIC	CS						
Total Gate Charge		Q <sub>G</sub>	$V_{DS}$ = 100 V, $I_D$ = 5.0A, $I_D$ = 1mA, $V_{GS}$ = 10 V		14.5		nC
Gate-Source Charge		Q <sub>GS</sub>			7.2		nC
Gate-Drain Charge		Q <sub>GD</sub>	(Note 1, 2)		2.5		nC
Turn-On Delay Time		t <sub>D(ON)</sub>			46		ns
Turn-On Rise Time		t <sub>R</sub>	V <sub>DD</sub> = 30V, I <sub>D</sub> = 5.0A, V <sub>GS</sub> = 10V		25		ns
Turn-Off Delay Time		t <sub>D(OFF)</sub>	R <sub>G</sub> = 25Ω (Note 1, 2)		114		ns
Turn-Off Fall Time		t <sub>F</sub>			27		ns
DRAIN-SOURCE DIODE CHAR	ACTERISTI	CS AND MAX	(IMUM RATINGS				
Maximum Continuous Drain-Source Diode		I <sub>S</sub>				5	А
Forward Current						5	А
Maximum Pulsed Drain-Source Diode		I <sub>SM</sub>				20	А
Forward Current						20	А
Drain-Source Diode Forward Voltage		$V_{SD}$	V <sub>GS</sub> = 0 V, I <sub>S</sub> = 5A			1.4	V
Body Diode Reverse Recovery Time		t <sub>rr</sub>	I <sub>S</sub> =5.0A, V <sub>GS</sub> =0V,		280		nS
Body Diode Reverse Recovery C	harge	Qrr	dI <sub>F</sub> /dt=100A/µs		3.0		μC
Note: 1 Pulse Test: Pulse width		$\frac{1}{2}$					


Note: 1. Pulse Test: Pulse width  $\leq$  300µs, Duty cycle  $\leq$  2%


2. Essentially independent of operating temperature.




#### TEST CIRCUITS AND WAVEFORMS













## 5N65K-MTQ


#### ■ TEST CIRCUITS AND WAVEFORMS (Cont.)



**Switching Test Circuit** 




Switching Waveforms




**Gate Charge Test Circuit** 

**Gate Charge Waveform** 



**Unclamped Inductive Switching Test Circuit** 



**Unclamped Inductive Switching Waveforms** 



UTC assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all UTC products described or contained herein. UTC products are not designed for use in life support appliances, devices or systems where malfunction of these products can be reasonably expected to result in personal injury. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice.

