UNISONIC TECHNOLOGIES CO., LTD

14N50 Power MOSFET

14A, 500V N-CHANNEL POWER MOSFET

DESCRIPTION


The UTC 14N50 is a N-Channel enhancement mode power MOSFET. The device adopts planar stripe and uses DMOS technology to minimize and provide lower on-state resistance and faster switching speed. It can also withstand high energy pulse under the avalanche and commutation mode conditions.

The UTC 14N50 is ideally suitable for high efficiency switch mode power supply, power factor correction and electronic lamp ballast based on half bridge topology.

FEATURES

- * $R_{DS(ON)}$ < 0.50 Ω @ V_{GS} = 10V, I_{D} = 7A
- * Ultra low gate charge (typical 43nC)
- * Low reverse transfer Capacitance (C_{RSS} = typical 20pF)
- * Fast switching capability
- * Avalanche energy tested
- * Improved dv/dt capability, high ruggedness


SYMBOL




ORDERING INFORMATION

Ordering Number		Dackago	Pin Assignment			Dooking	
Lead Free	Halogen Free	Package	1	2	3	Packing	
14N50L-TA3-T	14N50G-TA3-T	TO-220	G	D	S	Tube	
14N50L-TF1-T	14N50G-TF1-T	TO-220F1	G	D	S	Tube	
14N50L-TQ2-T	14N50G-TQ2-T	TO-263	G	D	S	Tube	
14N50L-TQ2-R	14N50G-TQ2-R	TO-263	G	D	S	Tape Reel	


Pin Assignment: G: Gate S: Source Note: D: Drain





www.unisonic.com.tw 1 of 7

■ MARKING



14N50

■ **ABSOLUTE MAXIMUM RATINGS** (T_C = 25°C, unless otherwise specified)

PARAMETER		SYMBOL	RATINGS	UNIT	
Drain-Source Voltage		V_{DSS}	500	V	
Gate-Source Voltage		V_{GSS}	±30	V	
Continuous Drain Current		I _D	14	Α	
Pulsed Drain Current (Note 2)		I _{DM}	48	Α	
Avalanche Current (Note 2)		I _{AR}	14	Α	
Single Pulsed Avalanche Energy (Note 3)		E _{AS}	400	mJ	
Peak Diode Recovery dv/dt (Note 4)		dv/dt	4.5	V/ns	
Power Dissipation (T _C =25°C)	TO-220		150	W	
	TO-220F1	P_D	50	W	
	TO-263		150	W	
Junction Temperature		TJ	+150	°C	
Storage Temperature		T _{STG}	-55~+150	°C	

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.

- 2. Repetitive Rating: Pulse width limited by maximum junction temperature.
- 3. L = 9.3mH, I_{AS} = 13A, V_{DD} = 50V, R_{G} = 25 Ω ,Starting T_{J} = 25 $^{\circ}$ C
- 4. $I_{SD} \le 13.A$, di/dt $\le 200A/\mu s$, $V_{DD} \le BV_{DSS}$, Starting $T_J = 25$ °C

■ THERMAL DATA

PARAMETER		SYMBOL	RATINGS	UNIT
Junction to Ambient		θ_{JA}	62.5	°C/W
	TO-220		0.83	°C/W
Junction to Case	TO-220F1	θ_{JC}	2.5	°C/W
	TO-263		0.83	°C/W


■ **ELECTRICAL CHARACTERISTICS** (T_C =25°C, unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT	
OFF CHARACTERISTICS							
Drain-Source Breakdown Voltage	BV _{DSS}	$V_{GS} = 0V$, $I_D = 1mA$	500			V	
Drain-Source Leakage Current	I _{DSS}	$V_{DS} = 500V, V_{GS} = 0V$			10	μΑ	
Cata Cauras Laglaga Current	I _{GSS}	$V_{GS} = 20V, V_{DS} = 0V$			100	nA	
Gate-Source Leakage Current		$V_{GS} = -20V, V_{DS} = 0V$			-100	nA	
Breakdown Voltage Temperature Coefficient	$\triangle BV_{DSS}/\triangle T_{J}$	I _D =250mA,Referenced to 25°C		0.5		V/°C	
ON CHARACTERISTICS							
Gate Threshold Voltage	$V_{GS(TH)}$	$V_{DS} = V_{GS}, I_D = 100 \mu A$ $V_{GS} = 10V, I_D = 7A$		3.75	4.5	V	
Static Drain-Source On-State Resistance	R _{DS(ON)}				0.50	Ω	
DYNAMIC CHARACTERISTICS							
Input Capacitance	C _{ISS}	-V _{DS} =25V, V _{GS} =0V, -f=1.0MHz		2000		pF	
Output Capacitance	Coss			238		pF	
Reverse Transfer Capacitance	C_{RSS}			55		pF	
SWITCHING CHARACTERISTICS							
Total Gate Charge	Q_G	V _{DS} =400V, I _D =12A, -V _{GS} =10 V (Note 1,2)		69	92	nC	
Gate-Source Charge	Q_GS			12		nC	
Gate-Drain Charge	Q_{GD}			31		nC	
Turn-On Delay Time	t _{D(ON)}	V_{DD} =250V, I_{D} =14A, R_{G} =25 Ω (Note 1,2)		24		nS	
Turn-On Rise Time	t _R			70		nS	
Turn-Off Delay Time	t _{D(OFF)}			54		nS	
Turn-Off Fall Time	t_{F}			50		nS	
DRAIN-SOURCE DIODE CHARACTERISTIC	CS AND MAXII	MUM RATINGS			ā.		
Drain-Source Diode Forward Voltage	V_{SD}	$V_{GS} = 0V, I_{S} = 14A$			1.6	V	
Maximum Continuous Drain-Source Diode	1				14	۸	
Forward Current	I _S				14	Α	
Maximum Pulsed Drain-Source Diode	la				56	Α	
Forward Current	I _{SM}				50	^	
Reverse Recovery Time	t _{rr}	$V_{GS} = 0V, I_{S} = 14A,$		470		nS	
Reverse Recovery Charge	Q_{RR}	dI _F / dt =100A/µs (Note 1)		3.1		μC	


Notes: 1. Pulse Test : Pulse width ≤ 300µs, Duty cycle ≤ 2%.

^{2.} Essentially independent of operating ambient temperature.

■ TEST CIRCUITS AND WAVEFORMS





Peak Diode Recovery dv/dt Test Circuit



Peak Diode Recovery dv/dt Waveforms


■ TEST CIRCUITS AND WAVEFORMS (Cont.)






Switching Test Circuit


Switching Waveforms






Gate Charge Test Circuit

Gate Charge Waveform





Unclamped Inductive Switching Test Circuit

Unclamped Inductive Switching Waveforms

14N50 Power MOSFET

UTC assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all UTC products described or contained herein. UTC products are not designed for use in life support appliances, devices or systems where malfunction of these products can be reasonably expected to result in personal injury. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice.