
BZX 2C

SILICON PLANAR POWER ZENER DIODES

Silicon Planar Power Zener Diodes

for use in stabilizing and clipping circuits with high power rating. The Zener voltages are graded according to the international E 24 standard. Other voltage tolerances and higher Zener voltages upon request.



Glass case ≈ JEDEC DO-41

Dimensions in mm

Absolute Maximum Ratings

| | Symbol | Value | Unit |
|---|------------------|--------------|------|
| Power Dissipation at T _{amb} = 25 °C | P _{tot} | 21) | W |
| Junction Temperature | T, | 175 | °C |
| Storage Temperature Range | T _s | -65 to + 175 | °C |

Characteristics at $T_{amb} = 25$ °C

| | Symbol | Min. | Тур. | Max. | Unit |
|--|----------------|------|------|------|------|
| Forward Voltage at I _F = 200 mA | V _F | - | - | 1.2 | V |





BZX 2C 2W SILICON PLANAR POWER ZENER DIODES

Characteristics at T_i = 25 °C

| TYPE | Nomonal Zener Voltage | Zener Voltag Range | e | Dynamic Resistance | | e | Revese Leakage Current (I _R at V _R) | | Maximum DC Zener Current |
|-----------|-----------------------------|-----------------------|-------------------------|--------------------|--------|-------------------------|---|--------------------|--------------------------------|
| BZX2C | V | V | I _{z⊤} (mA) | Ohm at | Ohm at | I _{zk} (mA) | I _R (uA) | V _R (V) | mA |
| BZX2C3V6 | 3.6 | 3.4 3.8 | 139 | 5.0 | 400 | 1.0 | 80 | 1.0 | 504 |
| BZX2C3V9 | 3.9 | 3.7 4.1 | 128 | 5.0 | 400 | 1.0 | 30 | 1.0 | 468 |
| BZX2C4V3 | 4.3 | 4.0 4.6 | 116 | 4.5 | 400 | 1.0 | 20 | 1.0 | 434 |
| BZX2C4V7 | 4.7 | 4.4 5.0 | 106 | 4.5 | 550 | 1.0 | 5.0 | 1.0 | 386 |
| BZX2C5V1 | 5.1 | 4.8 5.4 | 98 | 3.5 | 600 | 1.0 | 5.0 | 1.0 | 356 |
| BZX2C5V6 | 5.6 | 5.2 6.0 | 89.5 | 2.5 | 500 | 1.0 | 5.0 | 2.0 | 324 |
| BZX2C6V2 | 6.2 | 5.8 6.6 | 80.5 | 1.5 | 700 | 1.0 | 5.0 | 3.0 | 292 |
| BZX2C6V8 | 6.8 | 6.4 7.2 | 73.5 | 2.0 | 700 | 1.0 | 5.0 | 4.0 | 266 |
| BZX2C7V5 | 7.5 | 7.0 7.9 | 66.5 | 2.0 | 700 | 0.5 | 5.0 | 5.0 | 242 |
| BZX2C8V2 | 8.2 | 7.7 8.7 | 61.0 | 2.3 | 700 | 0.5 | 5.0 | 6.0 | 220 |
| BZX2C9V1 | 9.1 | 8.5 9.6 | 55.0 | 2.5 | 700 | 0.5 | 2.0 | 7.0 | 200 |
| BZX2C10V | 10 | 9.4 10.6 | 50.0 | 3.5 | 700 | 0.25 | 3.0 | 7.6 | 182 |
| BZX2C11V | 11 | 10.4 11.6 | 45.5 | 4.0 | 700 | 0.25 | 1.0 | 8.4 | 166 |
| BZX2C12V | 12 | 11.4 12.7 | 41.5 | 4.5 | 700 | 0.25 | 1.0 | 9.1 | 152 |
| BZX2C13V | 13 | 12.4 14.1 | 38.5 | 5.0 | 700 | 0.25 | 0.5 | 9.9 | 138 |
| BZX2C15V | 15 | 13.8 15.6 | 33.4 | 7.0 | 700 | 0.25 | 0.5 | 11.4 | 122 |
| BZX2C16V | 16 | 15.3 17.1 | 31.2 | 8.0 | 700 | 0.25 | 0.3 | 12.2 | 114 |
| BZX2C18V | 18 | 16.8 19.1 | 27.8 | 10 | 750 | 0.25 | 0.5 | 13.7 | 100 |
| BZX2C20V | 20 | 18.8 21.2 | 25.0 | 11 | 750 | 0.25 | 0.5 | 15.2 | 90 |
| BZX2C22V | 22 | 20.8 23.3 | 22.8 | 12 | 750 | 0.25 | 0.5 | 16.7 | 82 |
| BZX2C24V | 24 | 22.8 25.6 | 20.8 | 13 | 750 | 0.25 | 0.5 | 18.2 | 76 |
| BZX2C27V | 27 | 25.1 28.9 | 18.5 | 18 | 750 | 0.25 | 0.5 | 20.6 | 68 |
| BZX2C30V | 30 | 28 32 | 16.6 | 20 | 1000 | 0.25 | 0.5 | 22.5 | 60 |
| BZX2C33V | 33 | 31 35 | 15.1 | 23 | 1000 | 0.25 | 0.5 | 25.1 | 55 |
| BZX2C36V | 36 | 34 38 | 13.9 | 25 | 100 | 0.25 | 0.5 | 27.4 | 50 |
| BZX2C39V | 39 | 37 41 | 12.8 | 30 | 1000 | 0.25 | 0.5 | 29.7 | 47 |
| BZX2C43V | 43 | 40 46 | 11.6 | 35 | 1500 | 0.25 | 0.5 | 32.7 | 43 |
| BZX2C47V | 47 | 44 50 | 10.6 | 40 | 1500 | 0.25 | 0.5 | 35.8 | 39 |
| BZX2C51V | 51 | 48 54 | 9.8 | 48 | 1500 | 0.25 | 0.5 | 38.8 | 36 |
| BZX2C56V | 56 | 52 60 | 9.0 | 55 | 2000 | 0.25 | 0.5 | 42.6 | 32 |
| BZX2C62V | 62 | 58 66 | 8.1 | 60 | 2000 | 0.25 | 0.5 | 47.1 | 29 |
| BZX2C68V | 68 | 64 72 | 7.4 | 75 | 2000 | 0.25 | 0.5 | 51.7 | 27 |
| BZX2C75V | 75 | 70 79 | 6.7 | 90 | 2000 | 0.25 | 0.5 | 56.0 | 24 |
| BZX2C82V | 82 | 77 87 | 6.1 | 100 | 3000 | 0.25 | 0.5 | 62.2 | 22 |
| BZX2C91V | 91 | 85 96 | 5.5 | 125 | 3000 | 0.25 | 0.5 | 69.2 | 20 |
| BZX2C100V | 100 | 94 106 | 5.0 | 175 | 3000 | 0.25 | 0.5 | 76 | 18 |
| BZX2C110V | 110 | 104 116 | 4.5 | 250 | 4000 | 0.25 | 0.5 | 83.6 | 17 |
| BZX2C120V | 120 | 114 127 | 4.2 | 325 | 4500 | 0.25 | 0.5 | 91.2 | 15 |
| BZX2C130V | 130 | 124 141 | 3.8 | 400 | 5000 | 0.25 | 0.5 | 98.8 | 14 |
| BZX2C150V | 150 | 138 156 | 3.3 | 575 | 6000 | 0.25 | 0.5 | 114.0 | 12 |
| BZX2C160V | 160 | 153 171 | 3.1 | 650 | 6500 | 0.25 | 0.5 | 121.6 | 11 |
| BZX2C180V | 180 | 168 191 | 2.8 | 725 | 7000 | 0.25 | 0.5 | 136.8 | 10 |
| BZX2C200V | 200 | 188 212 | 2.5 | 900 | 0.25 | 0.5 | 0.5 | 152.0 | 9.0 |

Tested with pulses tp = 20 ms.

²⁾ Valid provided that leads are kept at ambient temperature at a distance of 8 mm from case.



