INTEGRATED CIRCUITS

DATA SHEET

74LVT244A3.3V Octal buffer/line driver (3-State)

Product specification Supersedes data of 1995 Nov 14 IC23 Data Handbook





3.3V Octal buffer/line driver (3-State)

74LVT244A

FEATURES

- Octal bus interface
- 3-State buffers
- Output capability: +64mA/-32mA
- TTL input and output switching levels
- Input and output interface capability to systems at 5V supply
- Bus-hold data inputs eliminate the need for external pull-up resistors to hold unused inputs
- Power-up 3-State
- Live insertion/extraction permitted
- No bus current loading when output is tied to 5V bus
- Latch-up protection exceeds 500mA per JEDEC Std 17
- ESD protection exceeds 2000V per MIL STD 883 Method 3015 and 200V per Machine Model

DESCRIPTION

The LVT244A is a high-performance BiCMOS product designed for $V_{\rm CC}$ operation at 3.3V.

This device is an octal buffer that is ideal for driving bus lines. The device features two Output Enables ($\overline{OE}1$, $\overline{OE}2$), each controlling four of the 3-State outputs.


QUICK REFERENCE DATA

SYMBOL	PARAMETER	CONDITIONS T _{amb} = 25°C; GND = 0V	TYPICAL	UNIT
t _{PLH} t _{PHL}	Propagation delay nAx to nYx	$C_L = 50pF;$ $V_{CC} = 3.3V$	2.5 2.6	ns
C _{IN}	Input capacitance	V _I = 0V or 3.0V	4	pF
C _{OUT}	Output capacitance	Outputs disabled; $V_O = 0V$ or 3.0V	8	pF
I _{CCZ}	Total supply current	Outputs disabled; V _{CC} = 3.6V	0.13	mA

ORDERING INFORMATION

PACKAGES	TEMPERATURE RANGE	OUTSIDE NORTH AMERICA	NORTH AMERICA	DWG NUMBER
20-Pin Plastic SOL	-40°C to +85°C	74LVT244A D	74LVT244A D	SOT163-1
20-Pin Plastic SSOP Type II	-40°C to +85°C	74LVT244A DB	74LVT244A DB	SOT339-1
20-Pin Plastic TSSOP Type I	-40°C to +85°C	74LVT244A PW	7LVT244APW DH	SOT360-1

PIN CONFIGURATION




PIN DESCRIPTION

PIN NUMBER	SYMBOL	NAME AND FUNCTION
2, 4, 6, 8	1A0 – 1A3	Data inputs
11. 13, 15, 17	2A0 – 2A3	Data inputs
18, 16, 14, 12	1Y0 – 1Y3	Data outputs
9, 7, 5, 3	2Y0 – 2Y3	Data outputs
1, 19	10E, 20E	Output enables
10	GND	Ground (0V)
20	V _{CC}	Positive supply voltage


3.3V Octal buffer/line driver (3-State)

74LVT244A

LOGIC SYMBOL



LOGIC SYMBOL (IEEE/IEC)



FUNCTION TABLE

INP	INPUTS					
nOE1	nAx	nYx				
L	L	L				
L	Н	Н				
Н	Х	Z				

H = High voltage level

L = Low voltage level

X = Don't care

Z = High impedance "off" state

ABSOLUTE MAXIMUM RATINGS^{1, 2}

SYMBOL	PARAMETER	CONDITIONS	RATING	UNIT
V _{CC}	DC supply voltage		-0.5 to +4.6	V
VI	DC input voltage ³		−0.5 to +7.0	V
V _{OUT}	DC output voltage ³	Output in Off or High state	-0.5 to +7.0	V
1	DC output current	Output in Low state	128	mA
Гоит	De output current	Output in High state	-64	IIIA
I _{IK}	DC input diode current	V _I < 0	-50	mA
I _{OK}	DC output diode current	V _O < 0	-50	mA
T _{stg}	Storage temperature range		-65 to 150	°C

NOTES:

- Stresses beyond those listed may cause permanent damage to the device. These are stress ratings only and functional operation of the
 device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to
 absolute-maximum-rated conditions for extended periods may affect device reliability.
- The performance capability of a high-performance integrated circuit in conjunction with its thermal environment can create junction temperatures which are detrimental to reliability. The maximum junction temperature of this integrated circuit should not exceed 150°C.

3. The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

3.3V Octal buffer/line driver (3-State)

74LVT244A

RECOMMENDED OPERATING CONDITIONS

SYMBOL	PARAMETER	LIM	UNIT	
STWIBOL	FARAMETER	MIN	MAX	ONIT
V _{CC}	DC supply voltage	2.7	3.6	V
VI	Input voltage	0	5.5	V
V _{IH}	High-level input voltage	2.0		V
V _{IL}	Low-level input voltage		0.8	V
I _{OH}	High-level output current		-32	mA
lau	Low-level output current		32	mA
loL	Low-level output current; current duty cycle ≤ 50%, f ≥ 1kHz		64	ША
Δt/Δν	Input transition rise or fall rate; outputs enabled		10	ns/V
T _{amb}	Operating free-air temperature range	-40	+85	°C

DC ELECTRICAL CHARACTERISTICS

					LIMITS			
SYMBOL	PARAMETER	TEST CONDITIONS		Temp =	: -40°C to +	-85°C	UNIT	
				MIN	TYP ¹	MAX		
V _{IK}	Input clamp voltage	$V_{CC} = 2.7V; I_{IK} = -18mA$			-0.9	-1.2	V	
		$V_{CC} = 2.7 \text{ to } 3.6 \text{V}; I_{OH} = -100 \mu\text{A}$		V _{CC} -0.2	V _{CC} -0.1			
V _{OH}	High-level output voltage	$V_{CC} = 2.7V; I_{OH} = -8mA$		2.4	2.5		V	
		$V_{CC} = 3.0V; I_{OH} = -32mA$		2.0	2.2			
		$V_{CC} = 2.7V; I_{OL} = 100\mu A$			0.1	0.2		
		V _{CC} = 2.7V; I _{OL} = 24mA			0.3	0.5		
V_{OL}	Low-level output voltage	V _{CC} = 3.0V; I _{OL} = 16mA			0.25	0.4	V	
		V _{CC} = 3.0V; I _{OL} = 32mA			0.3	0.5		
		V _{CC} = 3.0V; I _{OL} = 64mA			0.4	0.55		
		V _{CC} = 0 or 3.6V; V _I = 5.5V			0.1	10		
1.	Input leakage current	$V_{CC} = 3.6V$; $V_I = V_{CC}$ or GND	Control pins		±0.1	±1	μΑ	
H _I	Imput leakage current	$V_{CC} = 3.6V; V_I = V_{CC}$	Data Pins ⁴		0.1	1	μ, τ	
		$V_{CC} = 3.6V; V_I = 0$	Data i ilis		-1	-5		
I _{OFF}	Output off current	$V_{CC} = 0V$; V_{I} or $V_{O} = 0$ to 4.5V			1	±100	μΑ	
		$V_{CC} = 3V; V_I = 0.8V$		75	150			
I _{HOLD}	Bus Hold current A inputs ⁶	$V_{CC} = 3V; V_I = 2.0V$		- 75	-150		μΑ	
		$V_{CC} = 0V \text{ to } 3.6V; V_{CC} = 3.6V$		±500				
I _{EX}	Current into an output in the High state when V _O > V _{CC}	$V_{O} = 5.5V; V_{CC} = 3.0V$			60	125	μА	
I _{PU/PD}	Power up/down 3-State output current ³	$V_{CC} \le 1.2V$; $V_O = 0.5V$ to V_{CC} ; $V_I = GNI$ OE/ \overline{OE} = Don't care	O or V _{CC} ;		±1	±100	μА	
I _{OZH}	3-State output high current	$V_{CC} = 3.6V$; $V_O = 3V$; $V_I = V_{IL}$ or V_{IH}			1	5	μΑ	
I _{OZL}	3-State output low current	$V_{CC} = 3.6V$; $V_O = 0.5V$; $V_I = V_{IL}$ or V_{IH}			-1	- 5	μΑ	
I _{CCH}		$V_{CC} = 3.6V$; Outputs High, $V_I = GND$ or	V _{CC} , I _O = 0		0.13	0.19		
I _{CCL}	Quiescent supply current	$V_{CC} = 3.6V$; Outputs Low, $V_I = GND$ or $V_{CC} = 0.00$	V _{CC} , I _O = 0		3	12	mA	
I _{CCZ}	1	V _{CC} = 3.6V; Outputs Disabled; V _I = GNI	O or V_{CC} , $I_{O} = 0^{5}$		0.13	0.19		
Δl _{CC}	Additional supply current per input pin ²	V_{CC} = 3V to 3.6V; One input at V_{CC} -0.6 Other inputs at V_{CC} or GND	V,		0.1	0.2	mA	

NOTES:

- All typical values are at T_{amb} = 25°C.
 This is the increase in supply current for each input at the specified voltage level other than V_{CC} or GND
 This parameter is valid for any V_{CC} between 0V and 1.2V with a transition time of up to 10msec. From V_{CC} = 1.2V to V_{CC} = 3.3V ± 0.3V and 1.2V with a transition time of up to 10msec. From V_{CC} = 1.2V to V_{CC} = 3.3V ± 0.3V and 1.2V with a transition time of up to 10msec. From V_{CC} = 1.2V to V_{CC} = 3.3V ± 0.3V and 1.2V with a transition time of up to 10msec. From V_{CC} = 1.2V to V_{CC} = 3.3V ± 0.3V and 1.2V with a transition time of up to 10msec. From V_{CC} = 1.2V to V_{CC} = 3.3V ± 0.3V and 1.2V with a transition time of up to 10msec. From V_{CC} = 1.2V to V_{CC} = 3.3V ± 0.3V and 1.2V with a transition time of up to 10msec. From V_{CC} = 1.2V to V_{CC} = 3.3V ± 0.3V and 1.2V with a transition time of up to 10msec. From V_{CC} = 1.2V to V_{CC} = 3.3V ± 0.3V and 1.2V with a transition time of up to 10msec. transition time of 100 μ sec is permitted. This parameter is valid for T_{amb} = 25 $^{\circ}$ C only.
- 4. Unused pins at V_{CC} or GND.
 5. I_{CCZ} is measured with outputs pulled to V_{CC} or GND.
- 6. This is the bus hold overdrive current required to force the input to the opposite logic state.

3.3V Octal buffer/line driver (3-State)

74LVT244A

AC CHARACTERISTICS


GND = 0V; t_R = t_F = 2.5ns; C_L = 50pF; R_L = 500 Ω ; T_{amb} = -40°C to +85°C.

				L	IMITS		
SYMBOL	PARAMETER	WAVEFORM	٧ _c	_{CC} = 3.3V ±0.3	3V	V _{CC} = 2.7V	UNIT
			MIN	TYP ¹	MAX	MAX	
t _{PLH} t _{PHL}	Propagation delay nAx to nYx	1	1 1	2.5 2.6	4.1 4.1	5.0 5.1	ns
t _{PZH} t _{PZL}	Output enable time to High and Low level	2	1 1.1	3.2 3.1	5.2 5.2	6.3 6.7	ns
t _{PHZ}	Output disable time from High and Low level	2	1.9 1.8	3.3 3.3	5.6 5.1	6.3 5.6	ns


NOTE:

AC WAVEFORMS

 $V_M = 1.5V$, $V_{IN} = GND$ to 2.7V



Waveform 1. Input (nAx) to Output (nYx) Propagation Delays




Waveform 2. 3-State Output Enable and Disable Times

^{1.} All typical values are at V_{CC} = 3.3V and T_{amb} = 25°C.

3.3V Octal buffer/line driver (3-State)

74LVT244A

TEST CIRCUIT AND WAVEFORMS



TEST	SWITCH
t _{PLH} /t _{PHL}	Open
t _{PLZ} /t _{PZL}	6V
t _{PHZ} /t _{PZH}	GND

DEFINITIONS

R_L = Load resistor; see AC CHARACTERISTICS for value.

 C_L = Load capacitance includes jig and probe capacitance; see AC CHARACTERISTICS for value.

 $R_T = Termination resistance should be equal to <math>Z_{OUT}$ of pulse generators.

FAMILY	IN	PUT PULSE R	EQUIRE	MENTS	
FAMILI	Amplitude	Rep. Rate	t _W	t _R	t _F
74LVT	2.7V	≤10MHz	500ns	≤2.5ns	≤2.5ns


SV00092

3.3V Octal buffer/line driver (3-State)

74LVT244A

SO20: plastic small outline package; 20 leads; body width 7.5 mm

SOT163-1



DIMENSIONS (inch dimensions are derived from the original mm dimensions)

UNIT	A max.	A ₁	A ₂	A ₃	bp	O	D ⁽¹⁾	E ⁽¹⁾	е	HE	L	Lp	Q	٧	w	у	z ⁽¹⁾	θ
mm	2.65	0.30 0.10	2.45 2.25	0.25	0.49 0.36	0.32 0.23	13.0 12.6	7.6 7.4	1.27	10.65 10.00	1.4	1.1 0.4	1.1 1.0	0.25	0.25	0.1	0.9 0.4	8°
inches	0.10	0.012 0.004	0.096 0.089	0.01	0.019 0.014	0.013 0.009	0.51 0.49	0.30 0.29	0.050	0.42 0.39	0.055	0.043 0.016	0.043 0.039	0.01	0.01	0.004	0.035 0.016	o°

1. Plastic or metal protrusions of 0.15 mm maximum per side are not included.


OUTLINE		REFER	REFERENCES EUROPEAN				
VERSION	IEC JEDEC EI		EIAJ		PROJECTION ISSUE DATE		
SOT163-1	075E04	MS-013AC				-92-11-17 95-01-24	

3.3V Octal buffer/line driver (3-State)

74LVT244A

SSOP20: plastic shrink small outline package; 20 leads; body width 5.3 mm

SOT339-1



DIMENSIONS (mm are the original dimensions)

UNIT	A max.	Α1	A ₂	A ₃	bр	С	D ⁽¹⁾	E ⁽¹⁾	е	HE	L	Lp	Ø	v	w	у	Z ⁽¹⁾	θ
mm	2.0	0.21 0.05	1.80 1.65	0.25	0.38 0.25	0.20 0.09	7.4 7.0	5.4 5.2	0.65	7.9 7.6	1.25	1.03 0.63	0.9 0.7	0.2	0.13	0.1	0.9 0.5	8° 0°

Note

1. Plastic or metal protrusions of 0.20 mm maximum per side are not included.


OUTLINE		REFER	RENCES	EUROPEAN	ISSUE DATE
VERSION	IEC	JEDEC	EIAJ	PROJECTION	1990E DATE
SOT339-1		MO-150AE			-93-09-08- 95-02-04


3.3V Octal buffer/line driver (3-State)

74LVT244A

TSSOP20: plastic thin shrink small outline package; 20 leads; body width 4.4 mm

SOT360-1





DIMENSIONS (mm are the original dimensions)

UNIT	A max.	A ₁	A ₂	A ₃	рb	С	D ⁽¹⁾	E ⁽²⁾	е	HE	L	Lp	Q	v	w	у	Z ⁽¹⁾	θ
mm	1.10	0.15 0.05	0.95 0.80	0.25	0.30 0.19	0.2 0.1	6.6 6.4	4.5 4.3	0.65	6.6 6.2	1.0	0.75 0.50	0.4 0.3	0.2	0.13	0.1	0.5 0.2	8° 0°

Notes

- 1. Plastic or metal protrusions of 0.15 mm maximum per side are not included.
- 2. Plastic interlead protrusions of 0.25 mm maximum per side are not included.

OUTLINE		REFER	ENCES	EUROPEAN	ISSUE DATE
VERSION	IEC	JEDEC	EIAJ	PROJECTION	1550E DATE
SOT360-1		MO-153AC			-93-06-16- 95-02-04

3.3V Octal buffer/line driver (3-State)

74LVT244A

Data sheet status

Data sheet status	Product status	Definition [1]
Objective specification	Development	This data sheet contains the design target or goal specifications for product development. Specification may change in any manner without notice.
Preliminary specification	Qualification	This data sheet contains preliminary data, and supplementary data will be published at a later date. Philips Semiconductors reserves the right to make chages at any time without notice in order to improve design and supply the best possible product.
Product specification	Production	This data sheet contains final specifications. Philips Semiconductors reserves the right to make changes at any time without notice in order to improve design and supply the best possible product.

^[1] Please consult the most recently issued datasheet before initiating or completing a design.

Definitions

Short-form specification — The data in a short-form specification is extracted from a full data sheet with the same type number and title. For detailed information see the relevant data sheet or data handbook.

Limiting values definition — Limiting values given are in accordance with the Absolute Maximum Rating System (IEC 134). Stress above one or more of the limiting values may cause permanent damage to the device. These are stress ratings only and operation of the device at these or at any other conditions above those given in the Characteristics sections of the specification is not implied. Exposure to limiting values for extended periods may affect device reliability.

Application information — Applications that are described herein for any of these products are for illustrative purposes only. Philips Semiconductors make no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Disclaimers

Life support — These products are not designed for use in life support appliances, devices or systems where malfunction of these products can reasonably be expected to result in personal injury. Philips Semiconductors customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Philips Semiconductors for any damages resulting from such application.

Right to make changes — Philips Semiconductors reserves the right to make changes, without notice, in the products, including circuits, standard cells, and/or software, described or contained herein in order to improve design and/or performance. Philips Semiconductors assumes no responsibility or liability for the use of any of these products, conveys no license or title under any patent, copyright, or mask work right to these products, and makes no representations or warranties that these products are free from patent, copyright, or mask work right infringement, unless otherwise specified.

Philips Semiconductors 811 East Arques Avenue P.O. Box 3409 Sunnyvale, California 94088–3409 Telephone 800-234-7381 © Copyright Philips Electronics North America Corporation 1998 All rights reserved. Printed in U.S.A.

print code Date of release: 05-96

Document order number: 9397-750-03519

Let's make things better.

Philips Semiconductors



