



# 6.2×6.3mm Type (Surface Mount) SKHU Series

Part number		SKHUALE010	
Туре		Surface mount	
Operating force		1.57N	
Operating direction		Top push	
Travel		0.25mm	
Operating life (5mA 5V DC)		300,000 cycles	
Initial contact resistance		100mΩ max.	
Stem color		Black	
Stem height		2.5mm	
Series type		Sharp feeling type	
Operating temperature range		-30℃ to +85℃	
Rating (max.)		50mA 12V DC	
Rating (min.)		10µA 1V DC	
Electrical performance	Insulation resistance 100M $\Omega$ min. 100V DC for 1min.		
	Voltage proof	250V AC for 1 min.	
Durability	Vibration	10 to 55 to 10Hz/min., the amplitude is 1.5mm for all the frequencies, in the 3 direction of X, Y and Z for 2 hours respectively	
Environmental performance	Cold	-30±2℃ for 96h	
	Dry heat	80±2℃ for 96h	
	Damp heat	60±2℃, 90 to 95%RH for 96h	
Minimum order unit (pcs.)	Japan	3,000	
	Export	3,000	


### Photo Stem color : Black




### Dimensions



Land Dimensions




## Circuit Diagram



## Packing Specifications

Taping



Number of packages (pcs.)	es 1 reel	3,000
	1 case / Japan	30,000
	1 case / export packing	30,000
Tape width (mm)		12
Export package measurements (mm)		395×395×205

## Soldering Conditions

#### **Condition for Reflow**


1. Heating method

Double heating method with infrared heater.

2. Temperature measurement

Thermocouple 0.1 to 0.2  $\Phi$  CA(K) or CC(T) at solder joints (copper foil surface). A heat resisting tape should be used for fix measurement.

3. Temperature profile



Time inside soldering equipment

(1) The above temperature shall be measured of the top of switch. There are cases where PC board's temperature greatly differs from that of the switch, depending on the material, size, thickness of PC board's and others. Care, should be taken to prevent the switch's surface temperature from exceeding  $260^{\circ}$ C.

(2) Soldering conditions differ depending on reflow soldering machines. Prior verification of soldering condition is highly recommended.

#### **Manual Soldering**

Items	Condition
Soldering temperature	350℃ max.
Duration of soldering	3s max.
Capacity of soldering iron	60W max.

1. Consult with us for availability of TACT switch<sup>™</sup> washing.

- 2. Prevent flux penetration from the top side of the TACT switch<sup>™</sup>.
- 3. Switch terminals and a PC board should not be coated with flux prior to soldering.
- 4. The second soldering should be done after the switch returns to normal temperature.

Notes are common to this series/models.

- 1. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
- 2. Please place purchase orders for taping products per minimum order unit (1 reel or a case).
- 3. For  $\phi$ 330mm diameter reel requirements, please contact us.
- 4. This products can be used in vehicles. Although these products are designed to perform over a wide operating temperature range, please

ensure that you receive and read the formal delivery specifications before use.